



M12 FUEL™

M12 FBFL13-402B

M12 FUEL™ BAND FILE 13 MM

Worlds first cordless 12V band file with a capacity of 13mm belt width
Lightest cordless band file on the market, only 1.1 kg with a 2.0 Ah battery

Outperforms pneumatic competitor while providing better balance

2 speed modes and variable speed trigger provide maximum control from taking down welds to precise work with inox, aluminium and wood

Reverse mode allows the user to choose the belt orientation to manage the direction of sparks/ chips

One-hand design allows working in tight areas and ideal for overhead work

360° tool-free head adjustment allows the best handling for each working environment and provides compact storage

Dual action safety trigger with lock-on function for less strenuous on longer working periods

Tool-free belt change

LED lights up your work area for better visibility

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



No load speed (rpm)	0 - 7,200/ 0 - 14,500
Belt speed [m]/min	0- 560/ 0 - 1,105
Belt length (mm)	457
Belt width (mm)	13
Weight with battery pack (EPTA) (kg)	1.3 (M12 B4)
Kit included	2 x M12 B4 Battery packs, C12 C Charger, Tool bag
Article number	4933480961