


Electrical slide EGSK-26-100-2P

Part number: 562765

FESTO



 General operating condition

Data sheet

Feature	Value
Working stroke	100 mm
Size	26
Reversing backlash theoretical	$\leq 20 \mu\text{m}$
Spindle diameter	8 mm
Spindle pitch	2 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical linear axis With ball screw drive
Referencing	Reference switch
Spindle type	Ball screw drive
Symbol	00991211
Max. acceleration	10 m/s ²
Max. speed	0.28 m/s
Repetition accuracy	$\pm 0.01 \text{ mm}$
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C ... 40 °C
Dynamic basic load rating fixed bearing	1380 N
Dynamic basic load rating linear guide	5746 N
Dynamic basic load rating ball screw	2350 N
2nd moment of area Iy	17000 mm ⁴
2nd moment of area Iz	150000 mm ⁴
Max. drive torque	0.037 Nm
Max. force Fy	2223 N
Max. force Fz	2223 N
Max. moment Mx	37.8 Nm
Max. moment My	12.9 Nm
Max. moment Mz	12.9 Nm
Max. feed force Fx	116 N
Frictional torque independent of load	0.015 Nm
Static basic load rating ball screw	4020 N
Static basic load rating linear guide	12150 N
Mass moment of inertia JH per metre of stroke	0.0316 kgcm ²

Feature	Value
Mass moment of inertia JO	0.00357 kgcm ²
Feed constant	2 mm/U
Static basic load rating fixed bearing	1760 N
Reference service life	1000 km
Moving mass	153 g
Weight of slide	153 g
Product weight	1200 g
Weight of additional slide	153 g
Basic weight for 0 mm stroke	780 g
Additional weight per 10 mm stroke	42 g
Type of mounting	Via female thread and dowel pin
Material end cap	Die-cast aluminium Coated
Material profile	High-alloy stainless steel
Note on materials	RoHS-compliant
Material drive cover	Die-cast aluminium Coated
Material slide	Steel
Material spindle nut	Steel
Material spindle	Steel