

# STCLQ4LA1



CLQ LED 2D WH/OPAL SLFTST



## General Information

Extended Product Type	STCLQ4LA1
Product ID	7TCA091160R0566
EAN	5415022465891
Catalog Description	CLQ LED 2D WH/OPAL SLFTST
Long Description	Camarque Decorative LED Luminaire, M3, 220-240 AC 50/60Hz, 2 LED 20+2W, 1830/207 Lumens, Automatic Self Test, Environment 0-30 Degrees Celsius, White/Opal

## Ordering

EAN	5415022465891
Minimum Order Quantity	1 piece
Customs Tariff Number	9405608000

## Dimensions

Product Net Weight	2.136 kg
--------------------	----------

## Container Information

Package Level 1 EAN	30785991447263
Package Level 2 Units	1 piece
Package Level 2 Width	374.904 mm
Package Level 2 Height	130.048 mm
Package Level 2 Depth / Length	385.064 mm

## Additional Information

Product Main Type	STANDARD EMERGENCY LIGHTING
Product Name	LIGHTING
UPC	075114363426

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	STCLQ4LA1
Instructions and Manuals	STCLQ4LA1

—

**Classifications**

---

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

---

—

**Categories**

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

