


Geberit Mapress Stainless Steel T-piece, equal



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5

- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	arc °	L cm	L1 cm	I cm	Z cm	Z1 cm
33008	10	12	90	5.6	3.5	2.8	1.1	1.8
31002	12	15	90	6.4	3.9	3.2	1.2	1.9
31003	15	18	90	6.8	4.1	3.4	1.4	2.1
31004	20	22	90	7.4	4.4	3.7	1.6	2.3

Art. no.	DN	d _ø mm	arc °	L cm	L1 cm	I cm	Z cm	Z1 cm
31005	25	28	90	8.4	5	4.2	1.9	2.7
31006	32	35	90	10	5.7	5	2.4	3.1
31007	40	42	90	11.4	6.5	5.7	2.7	3.5
31008	50	54	90	13.8	7.7	6.9	3.4	4.2
31009	65	76.1	90	23	11	11.5	6.2	5.7
31010	80	88.9	90	26	12.7	13	7	6.7
31011	100	108	90	31	15.3	15.5	8	7.8