

V23079D1001B301

✓ ACTIVE

TE Internal #: 5-1393788-5

TE Internal Description: V23079D1001B301

Small Signal Relay, Axicom P2 Standard

[View on TE.com >](#)



All Small Signal Relay, Axicom P2 Standard (23)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 6-1393788-2
V23079D1011B301

TE Part # 7-1393788-6
V23079G1001B301

Customers Also Bought

TE Part #2-2071448-9
ORWH-SS-124H1FH,000

TE Part #1-5161390-0
10P.DIP SWITCH ASSY

TE Part #1-641974-1
12P UMNL PIN HDR ASSY BLK

TE Part #225242-E
M12 MALE, A CODE, RA, 5P THR FRONT MOUNT

TE Part #796949-7
7 POS TERMI-BLOK PCB MOUNT

TE Part #2029181-4
4P VAL-U-LOK VRTHDR W/PGS GW

TE Part #147444-1
SOCKET,MIN-SPR AU-AU SER-1

TE Part #3-647609-5
05P MTA100 HDR ASSY F/L LF

TE Part #4-1625867-0
RP 1J 0.166W 15R8 0.1% 25PPM 1K RL

TE Part #794783-1
04P UMNL HDR ASSY,BLACK

Documents

Product Drawings
V23079D1001B301

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_5-1393788-5_F1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1393788-5_F1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1393788-5_F1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Axicom Signal and High Frequency Relays \(RF Switches\) APPLICATION NOTE #2](#)

English

[Transportation, Storage, Handling, Assembly and Testing of AXICOM SMT Relays](#)

English

[P2 Relay Datasheet](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[UL](#)

English