

## 10 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

- Extends your VGA monitor cable

### Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

<b>Hardware</b>	Warranty	Lifetime
	Connector Plating	Nickel
<b>Connector(s)</b>	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Pin number 9 is not populated on these connectors
<b>Physical Characteristics</b>	Cable Length	3 m [10 ft]
	Color	Black
	Product Height	1.5 cm [0.6 in]
	Product Length	3 m [10 ft]
	Product Width	33.8 mm [1.3 in]
	Weight of Product	366 g [12.9 oz]
<b>Packaging Information</b>	Package Height	22 mm [0.9 in]
	Package Length	32.7 cm [12.9 in]
	Package Width	11.7 cm [4.6 in]
	Shipping (Package) Weight	378 g [13.3 oz]
<b>What's in the Box</b>	Included in Package	10 FOOT COAXIAL CABLE

Product appearance and specifications are subject to change without notice.