


ESG, Aluminum Electrolytic, 22 uF, 20%, 250 VDC, -40/+105°C, Lead Spacing = 5mm

**Dimensions**

D	13mm +/-0.5mm
L	20mm +2mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	2000

General Information

Supplier:	KEMET
Series:	ESG
Dielectric:	Aluminum Electrolytic
Description:	Long Life Single Ended Aluminum Electrolytic
Features:	Long Life
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC, 300 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	5000 Hrs
Dissipation Factor:	15.00% 120Hz 20C
Ripple Current:	160 mAmps (120Hz 105C)
Leakage Current:	340 uA (2min 20°C)
Impedance Ratio at -25C:	3
Impedance Ratio at -40C:	6