

PRODUCT-DETAILS

CR-S006/024VDC1SS

CR-S006/024VDC1SS Socket 1c/o, A1-A2=6-24VDC, 250VAC



General Information

Extended Product Type	CR-S006/024VDC1SS
Product ID	1SVR405521R1100
EAN	4013614499180
Catalog Description	CR-S006/024VDC1SS Socket 1c/o, A1-A2=6-24VDC, 250VAC
Long Description	CR-S006/024VDC1SS Socket 1c/o, A1-A2=6-24VDC, 250VAC screw terminals

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85369010

Popular Downloads

Data Sheet, Technical Information	2CDC110004C0210_05
Instructions and Manuals	1SVC405650M9010

Dimensions

Product Net Width	6.3 mm
Product Net Height	76.4 mm
Product Net Depth /	88.5 mm

Length	
Product Net Weight	0.025 kg

Technical

Function	Accessory for interface relays CR-S
Sub-Function	Socket
Rated Control Supply Voltage (U _s)	6 ... 24 V DC
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Operation -40 ... +70 °C Storage 0 ... +40 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Connecting Capacity UL/CSA	Flexible 14 AWG Rigid 14 AWG
Tightening Torque UL/CSA	4.42 in-lb

Certificates and Declarations (Document Number)

CSA Certificate	CSA_262671_2785566
cURus Certificate	cURus508_E244328
Declaration of Conformity - CE	1SVD982017-0001
EAC Certificate	EAC_RU_C-DE.ME77.B.00443-19
Environmental Information	1SAA981009-2403
Instructions and Manuals	1SVC405650M9010
RoHS Information	1SVD982017-0001
VDE Certificate	VDE_40039479

Container Information

Package Level 1 Units	box 10 piece
Package Level 1 Width	93 mm
Package Level 1 Height	81 mm
Package Level 1 Depth / Length	66 mm
Package Level 1 Gross Weight	0.26 kg
Package Level 1 EAN	4013614486319

Classifications

Object Classification Code	K
ETIM 4	EC001456 - Relay socket
ETIM 5	EC001456 - Relay socket
ETIM 6	EC001456 - Relay socket
ETIM 7	EC001456 - Relay socket

eClass	V11.0 : 27371603
UNSPSC	39122335
E-Number (Finland)	2712360
E-Number (Sweden)	4001390

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

