




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Tin (Sn)**
Wire Contact Termination Area Plating Material: **Pre-Tin**
Operating Voltage: **600 VAC**
Contact Retention Within Housing: **With**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Orientation	Straight
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Mating Square Post Dimension	1.14 mm[.045 in]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Type	Pin
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	9 A

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	1.5 – 3.1 mm[.06 – .122 in]
Wire Size	.33 – .82 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2825212-1
VAL-U-LOK PIN HCS TN 22-18 LP

TE Part # 794956-5
VAL-U-LOK SKT BR SN 18-22AWG

TE Part # 2415880-1
VAL-U-LOK PIN BR SN 22-18AWG

TE Part # 1586054-1
VAL-U-LOK PIN BR SN 16AWG

TE Part # 2825213-1
VAL-U-LOK SKT HCS SN 22-18 LP

TE Part # 2238018-1
VAL-U-LOK PIN BR SN 22-26AWG

TE Part # 2238021-1
VAL-U-LOK SKT BR SN 22-18 LP

TE Part # 794955-1
VAL-U-LOK PIN BR SN 22-18AWG

TE Part # 2825210-1
VAL-U-LOK PIN HCS SN 18-22AWG

TE Part # 2238022-1
VAL-U-LOK PIN BR SN 26-22 LP

TE Part # 2238017-1
VAL-U-LOK SKT BR SN 18-22AWG


TE Part # 2238016-1
VAL-U-LOK PIN BR SN 18-22AWG

TE Part # 794955-3
VAL-U-LOK PIN PHBZ SN 22-18AWG


Customers Also Bought



TE Part #1969608-2
2P VAL-U-LOK TPA 22-18 AWG




TE Part #3-350566-1
MINI AMP-IN 22-18 PTLP/PHBZ



TE Part #1969612-2
2P FH PLUG VAL-U-LOK V0



TE Part #1969608-4
4P VAL-U-LOK TPA 22-18 AWG




TE Part #1969614-2
2P RCPT VAL-U-LOK V0



TE Part #CJ4552-000
D-141-30-LF



TE Part #CP2527-000
RT-780-3/8-3-SP



TE Part #1-1969614-2
12P RCPT VAL-U-LOK V0



TE Part #1-1969608-2
12P VAL-U-LOK TPA 22-18 AWG



TE Part #014973-000
FCSM-28/9-1200-S(B25)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2238020-1_A_c-2238020-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2238020-1_A_c-2238020-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2238020-1_A_c-2238020-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

VDE Certificate

English