

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Pb (1% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [AMP GPR](#)



Connector Contacts(2)



Power Contacts(2)

Customers Also Bought




TE Part #1-200835-1  
SERIES"M" MIN. RECT. GUIDE SOC




TE Part #3-1617033-1  
HFW1230K06P = M39016/6-105P



TE Part #770147-1  
.093 CP&S PIN PTPBR LP 24-18



TE Part #YCTD126E01AC015000  
MODULE ASSY



TE Part #1877698-1  
Insert Asy,Pin, GPRBE3Q3PB



TE Part #1738171-1  
INSERT ASY,PIN,E,30-P,KEY B



TE Part #1738169-1  
INSERT ASY,SOCKET,E,30P,KEY A



TE Part #1738310-1  
STRAIN RELIEF KIT,STRT,GPRB1

Documents

Product Drawings

PIN CONT,SIZE 12,GPR

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1738017-1\_3.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1738017-1\_3.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1738017-1\_3.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



---

[Datasheets & Catalog Pages](#)  
[ARINC 600 Next Generation Receptacle Connector](#)  
English