

3240898

https://www.phoenixcontact.com/gb/products/3240898

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, metric thread, IP66 protection, straight

Commercial data

Item number	3240898
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 587 (C-3-2019)
GTIN	4046356710053
Weight per piece (including packing)	11.456 g
Weight per piece (excluding packing)	11.468 g
Customs tariff number	39174000
Country of origin	DE



3240898

https://www.phoenixcontact.com/gb/products/3240898

Technical data

Product properties

Product type	Protective hose screw connection
Application	Cable gland
Type of the screw connection	Conduit adapter
Туре	Outer thread
Cable outlet	straight
Thread type	metric

Dimensions

Width	29.5 mm
Height	44.5 mm
Wrench size	27 mm
Wrench size for mounting	27 mm

External dimensions

Outside diameter	16.5 mm

Material specifications

Material	PA 6
Flammability rating according to UL 94	V0
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Mechanical data

Type of the screw connection	Conduit adapter

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C 120 °C



3240898

https://www.phoenixcontact.com/gb/products/3240898

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/3240898



UL Recognized
Approval ID: E86359



LR



VDE approval of drawings



3240898

https://www.phoenixcontact.com/gb/products/3240898

Classifications

UNSPSC 21.0

ECLASS		
	ECLASS-13.0	27430311
Εī	ГІМ	
	ETIM 9.0	EC001178
UI	NSPSC	

39121300



3240898

https://www.phoenixcontact.com/gb/products/3240898

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk