



DCG404N-XJ

18 Volt Cordless Compact Angle Grinder

- Innovative compact series – maximum power in an exceptionally compact, ergonomic and functional design
- Paddle switch – for enhanced user safety
- Perform & Protect: Electronic brake and clutch – stops the wheel quickly and helps protect the user and tool in the event of a stall
- Compact die-cast gear housing for a large cutting depth – robust and durable
- 28% more compact than the DCG408 cordless angle grinder
- Rubber overmoulded grip and ergonomic, compact design with an optimised centre of gravity
- Vibration-damped side handle for a secure grip, with two mounting positions for added flexibility
- Mesh guard – helps protect the motor and electronics from dust and debris
- Optimised for POWERSTACK™ batteries – delivering maximum performance, compact size and long runtime; compatible with all DEWALT 18V XR batteries and DEWALT XR FLEXVOLT batteries
-

Standard scope of delivery

- Vibration-damped side handle
- Guard for cutting and grinding
- Quick-lock flange

Technical data

Battery technology	18 volt XR or XR Flexvolt batteries
No-load speed (min ⁻¹)	11.000
Max. disc diameter (mm)	125
Drive spindle	M14
Switch type	Paddle switch
Weight (without battery, in kg)	1,56
Triaxial vibration surface grinding (m/s ²)	8,9
Uncertainty factor K1 (m/s ²)	1,5
Sound pressure level (dB(A))	86
Sound power (dB(A))	94
Uncertainty factor (dB(A))	3
EAN-code	5035048834510