



NAUSB-W

Reversible USB 2.0 gender changer (type A and B), Nickel D-housing.

As digitization spreads, interface problems among audio/video networks, IT equipment, MP3 camcorders, etc. continue to increase.

Neutrik's reversible USB gender changer, mounted in the standardized D-shape housing, solves these issues.

Compatible with both standard USB patch cables and Neutrik's locking, pre-terminated NKUSB-* cable assemblies.

Features & Benefits

- Ideal for audio networking and integration of computerbased equipment into audio systems
- USB 2.0 gender changer type A-B (B-A)
- Universally accepted standard D-shape housing
- IP65 ingress protection in mated condition with NKUSB-* and SCDP-* sealing gasket
- Reversible insert offering type A or B on front or rear end

Technical Information

| Product | |
|------------------------|---------|
| Title | NAUSB-W |
| Connection Type | Adapter |
| Gender | female |

| Mechanical | |
|---------------------------|----------------------|
| Wiresize | |
| Mounting direction | Front mounting |
| Chassis shape | D |
| Lifetime | > 1000 mating cycles |

| Material | |
|------------------------|-------------------------|
| Contact plating | Au |
| Contacts | Brass (CuZn39Pb3) |
| Insert | PBTP 15 % GR |
| Shell | Zinc diecast (ZnAl4Cu1) |
| Shell plating | Nickel |

| Environmental | |
|----------------------------|------------------------|
| Flammability | UL 94 V-0 |
| Standard compliance | USB 2.0 specifications |
| Temperature range | -25 °C to +85 °C |