

JMO02 JALSKATE SAS

S3 SRC
EN ISO 20345:2011
35 to 47



- Full grain leather
- J-MODE PU / TPU transparent Sole
- Safety toe cap and midsole no metallic
- Antistatic

- ❖ Urban-style black shoe.
- ❖ Water-repellent full grain leather upper, pull-up finish. TPU Jallatte brand on the leather.
- ❖ Breathable upper lining in 3D mesh, with honeycomb structure for improved all-round ventilation of the foot and fast-drying.
- ❖ Vamp lining in non-woven fabric, resists scuffing and acid perspiration.
- ❖ Padded tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
- ❖ Padded ergonomic collar in compact flexible foam, lined for extra comfort and better ankle and Achilles tendon protection.
- ❖ Lace up on six pairs of eyelets. Laces : 120 cm. Leather lace-loop keeps tongue in place as you walk.
- ❖ Footbed **POLYJAL** single-block structure made of soft polyurethane and textile, anatomical, perforated in the front part and with heel shock absorbers.
- ❖ Ergonomic shoe with **broad synthetic polymer toe cap**, for saving on weight (50% lighter than steel) and removal of perspiration from around the forefoot. Impact resistance to **200 Joules**.
- ❖ New manufacturing **process** : antiperforation inner sole and insert in **FleXtane™ By Jallatte** material, antistatic, **100% composite**. Sewn directly onto the bootstrap and covering **100% of the foot** for all-round protection. **100% composite** materials: lighter than steel, non-magnetic, non-conductive of heat or cold.
- ❖ Heel stiffener to reinforce the heel seat
- ❖ Bi-component **Softane/ TPU transparent** sole. The expanded molecular structure of the Softane comfort layer ensures lightweight, supple footwear for walking.

Slip resistance tests results

EN Standard : EN ISO 20345 : 2011
Requirement SRC (SRA+SRB)

SRA Test ground : ceramic / lubricant : water and detergent
On flat **0,40** (>0,32) – On the heel **0,31** (>0,28)

SRB Test ground steel/lubricant : glycerine
On flat **0,30** (>0,18) – On the heel : **0,20** (>0,13)

- Thermoplastic PU transparent formulation over staples improves grip and offers excellent resistance to abrasion and very good grip in oil, fuel and grease.
- Central groove to channel away liquids and optimize adherence.
- Very flat sole with a large contact area with the ground. Improved stability
- Young look and maximum working comfort.
- Heel shock absorption 26 Joules

Weight	Gross weight (42): 1416 g / Net weight (42): 1229 g		
Size	35 to 39	40 to 45	46 to 47
Packaging	5 pairs	10 pairs	5 pairs
Dimensions (mm)	685 x 225 x 345	685 x 440 x 345	685 x 225 x 345
Dimensions box shoe (mm)	340 x 210 x 133		

