

TF-F550

Torque wrench TORCOFIX FS

without pre-set

Code	ETIM
3288269	EC002132
EAN	UNSPSC
4010886965597	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Controlled screw tightening in the range of 10 - 50 Nm / 7,5 - 37 lbf-ft
- Triggering and robust pipe torque wrench with fixed setting
- Versions with SE 14x18 insert socket
- For controlled right- and left-hand tightening (insert tool for change of direction)
- Proven and robust release mechanism
- Compact Design
- New ergonomic handle
- Tamper-proof Cap at the End of the Handle
- Factory depth gauge: 17.5 mm (9x12 mm)
- Operation only with end fittings with standardised depth gauges, otherwise inaccuracies can arise
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/-3 % deviation and thus with a greater precision than the standard-stipulated +/-4 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- If fixed setting at the factory is desired is required, please state the Nm / lbf-ft value when ordering (price on request)
- OPTIONAL: 2in1 Adjustment and Locking Tool TF-EFS25 (Code: 3254941)

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [lbf-ft]	7,5 lbf-ft - 37 lbf-ft
Net weight [kg]	0,27 kg	Drive connector rectangular	9 x 12 mm
Total length [mm]	246 mm	Backup	Catch lock
Total width [mm]	22 mm	Trigger mechanism	Short path triggering
Total height [mm]	18,5 mm	Precision +/-	+/- 3 %
Depth gauge [metric]	17,5 mm	Direction of tightening	Left and right
Torque (min.) [N·m]	10 Nm	Fixed setting	yes
Torque (max.) [N·m]	50 Nm	Test certificate	DIN EN ISO 6789-2:2017
Torque (min.) [lbf-ft]	7,5 lbf-ft	Calibration length	193,5 mm
Torque (max.) [lbf-ft]	37 lbf-ft	Storage/Content	Plastic box
Torque range (min./max.) [N·m]	10 Nm - 50 Nm		