

Swivel Stem Castor, grey rubber 80mm, 50kg

Swivel Stem Castor

PRODUCT

Article number	CP1FA080-322L10	CP1FD080-322L10
		

Product Details

Castor assembly : Pressed steel, zinc plated housing, with threaded stem fitting.
 Swivel : Swivel on two rows of balls
 Rim : Black Polypropylene.
 Tread : Grey synthetic Rubber. Non-marking.
 Hub : Plain bearing.

TECHNICAL DATA

Specifications	Threaded Stem
Wheel Diameter - ØD ± 1%	80 mm
Hub Type	Plain bore
Hub Length	24 mm ±1
Width of Tread	22mm ±1
Width of Tread-on floor	22 mm ±1
Overall Height	98 mm
Offset	22 mm
Fitted Stem Diameter	10 mm
Fitted stem Height	25 mm
Hardness of tread A ±3	A 80° Shore
Load capacity	50 Kg
Temperature	-5 / +50 °C

Applications :

Light-weight appliances and furniture.
 Quiet.
 Easy to assemble with the crimped stem.