



PLT3H-L



- For indoor use
- Versatile cable ties can be used in countless applications
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- A variety of materials and colors available for specific applications
- Miniature to Standard cross sections feature a curved tip for easy threading and handling

■ Part Number	PLT3H-L
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie, 11.4", Light-Heavy cross section
■ Product Type	Cable Ties
■ Material	Nylon 6.6
■ Color	Natural
■ CSA Certified	Yes
■ UL Listed (File #E56854)	Yes
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	11.4
■ Length (mm)	290
■ Width (In.)	.300
■ Width (mm)	7.6
■ CE Compliant	Yes
■ Cross Section	Light-Heavy
■ Head Height (In.)	.290
■ Head Height (mm)	7.4
■ Head Width (In.)	.480
■ Head Width (mm)	12.2
■ Locking Style	Locking
■ Material Flammability Rating	UL 94V-2
■ Max. Bundle Diameter (In.)	3.00
■ Max. Bundle Diameter (mm)	76
■ Max. Continuous Use Temperature	185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	120
■ Min. Loop Tensile Strength (N)	534

■ Pricing Description	Cable Tie, 11.4"L (290mm), Light-Heavy, Nylon, Natural
■ Thickness (In.)	.075
■ Thickness (mm)	1.9
■ Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
■ Min. Order UOM	PC
■ Min. Order Qty.	50
■ BOM Qty. (# of Pkgs.)	

