

ATP SD/SDHC/SDXC Card

Industrial Grade

Targeted Product Portfolio, Engineered Specifically for Your Mission Critical Applications



Key Features

- SD Life Monitor
- Advanced Wear Leveling
- SiP (System in Package)
- AutoRefresh technology
- Dynamic Data Refresh
- Power failure protection
- Industrial temperature
- Joint Validation
- 100% MP Level Test

Applications

- Industrial PC
- Medical devices
- Automation
- Automotive IVI systems
- Test and Measurement
- Surveillance systems
- Drive recorders
- Navigations
- Network cameras
- Mobile/Handheld computers

ATP SD cards are the ideal storage format for industrial and automotive applications as they can be conveniently inserted into and easily removed from small host devices for convenient data transfer and storage expansion.

Made to perform dependably under rigorous conditions, ATP SD cards are designed with extensive longevity, which is typically required in industrial applications such as automation, networking, health care and more.

ATP SD cards also deliver the quality, durability and reliability to meet the requirements of major automotive OEM/Tier 1 suppliers, system developers and service providers for higher levels of data accuracy, consistency and integrity in applications such as maps/navigation systems, in-vehicle infotainment (IVI), Advanced Driver Assistance Systems (ADAS), and other data-intensive applications. These solutions can withstand extreme temperatures, dust and shock/vibration, and maintain data integrity under power cycling or sudden power-off events.

Technologies & Add-On Services*		Life Monitor	Sudden Power-Off Recovery	Advanced Wear Leveling	AutoRefresh	Dynamic Data Refresh	Secure Erase	Industrial Temperature	System in Package	Complete Drive Test	Joint Validation
Product Line	Premium	Δ	●	●	●	Δ	●	●	●	●	Δ
	Superior	Δ	●	●	●	●	●	Δ	●	●	Δ
	Value			●					●		

Δ: Customization option available on a project basis.



Specifications

Product Name		SD/SDHC/SDXC				
Product Line		Premium			Superior	
Naming		S800Pi	S700Pi	S700Pi	S700Sc	S700Sc
Flash Type		SLC	iTemp SLC mode	iTemp 3D NAND SLC mode	SLC mode	3D NAND SLC mode
Density		512 MB to 8 GB	4 GB to 8 GB	8 GB to 32 GB	4 GB to 8 GB	8 GB to 32 GB
Performance	Sequential Read up to (MB/s)	70	76	99	76	99
	Sequential Write up to (MB/s)	39	50	64	50	64
Interface		512 MB ~ 2 GB, HS mode 4 GB ~ 8 GB, UHS-I	UHS-I	UHS-I	UHS-I	UHS-I
Operating Temperature		-40°C to 85°C			-25°C to 85°C	
Reliability	TBW* (max.)	192 TB	128 TB	256 TB	128 TB	256 TB
	MTBF @ 25°C	>5,000,000 hours	>3,000,000 hours			
	Number of Insertions:	20,000 (SDA spec minimum 10,000)				
Dimensions: L x W x H (mm)		32.0 x 24.0 x 2.1				

Product Name		SD/SDHC/SDXC				
Product Line		Superior				Value
Naming		S600Si	S600Sc	S600Sia	S600Sc	S600Vc
Flash Type		iTemp MLC / 3D NAND TLC	MLC	iTemp 3D NAND TLC	3D NAND TLC	3D NAND TLC
Density		8 GB to 256 GB**	8 GB to 256 GB**	32 GB to 128 GB	32 GB to 128 GB	32 GB to 128 GB
Performance	Sequential Read up to (MB/s)	96	96	94	94	80
	Sequential Write up to (MB/s)	78	78	54	54	76
Interface		UHS-I				
Operating Temperature		-40°C to 85°C	-25°C to 85°C	-40°C to 85°C	-25°C to 85°C	-25°C to 85°C
Reliability	TBW* (max.)	307 TB	307 TB	77 TB	77 TB	77 TB
	MTBF @ 25°C	>2,000,000 hours				>1,000,000 hours
	Number of Insertions:	20,000 (SDA spec minimum 10,000)				
Dimensions: L x W x H (mm)		32.0 x 24.0 x 2.1				

* Under highest Sequential write value. May vary by density, configuration and applications.

** By project support.

To learn more about this product, contact your ATP Representative.

ATP Global Footprint

ATP TAIWAN(HQ)

TEL: +886-2-2659-6368
FAX: +886-2-2659-4982
sales-apac@atpinc.com

ATP USA

TEL: +1-408-732-5000
FAX: +1-408-732-5055
sales@atpinc.com

ATP EUROPE

TEL: +49-89-374-9999-0
FAX: +49-89-374-9999-29
sales-europe@atpinc.com

ATP JAPAN

TEL: +81-3-6260-0797
FAX: +81-3-6260-0798
sales-japan@atpinc.com

ATP CHINA

TEL: +86-21-5080-2220
FAX: +86-21-9687-0000-026
sales@cn.atpinc.com