



SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 1

Revision date: 26/07/2017

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SAPPHIRE HI-POWER RANGE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Hydraulic and Compressor Oil

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements: This product has no label elements.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

[cont...]

SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 2

MINERAL OIL (NOTE L - LESS THAN 3% DMSO EXTRACT) - REACH registered number(s): 01-2119488706-23

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-090-8	64741-88-4	Substance with a Community workplace exposure limit.	-	50-70%

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT) - REACH registered number(s): 01-2119480472-38

265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	30-50%
-----------	------------	--	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

[cont...]

SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 3

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is exhaust ventilation of the area.
Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is exhaust ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves. Nitrile gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Blue

Odour: Barely perceptible odour

Evaporation rate: Negligible

[cont...]

SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 4

Oxidising:	Non-oxidising (by EC criteria)		
Solubility in water:	Insoluble		
Viscosity:	Oily		
Kinematic viscosity:	32 to 100		
Viscosity test method:	Kinematic viscosity in 10 ⁻⁶ m ² /s at 40°C (ISO 3104/3105)		
Boiling point/range°C:	No data available.	Melting point/range°C:	< -20
Flammability limits %:	lower: No data available.	upper:	No data available.
	Flash point°C: > 150	Part.coeff. n-octanol/water:	No data available.
	Autoflammability°C: > 150	Vapour pressure:	No data available.
	Relative density: 0.82	pH:	No data available.
	VOC g/l: 0		

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

- Skin contact:** There may be mild irritation at the site of contact.
- Eye contact:** There may be irritation and redness.
- Ingestion:** There may be irritation of the throat.
- Inhalation:** No symptoms.

[cont...]

SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 5

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 13 01 10

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

[cont...]

SAFETY DATA SHEET
SAPPHIRE HI-POWER RANGE

Page: 6

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.