



381252/I

Description: Dyed woven nylon & polyester oxford, non-breathable polyurethane coated with a water repellent finish.

Fabric: 210D Nylon/200D Polyester 26 x 23/cm.
85%Nylon 15%Polyester

Property	Test Method	Typical Result
Total Weight	+/-3%	143 g/m ²
Usable Width (cms)	Cut edge	93cms
Dimensional Change		2-3%
Spray Rating After 4 Wash 40°C		4-5 3-4
Tensile strength	ISO 13934-1	Warp: 1500N Weft: 1100N
Tear strength	ISO 13937-3	Warp: 80N Weft: 70N
Colour fastness to rubbing		4-5
Colour fastness to washing 40°C	ISO 105	4-5
Abrasion	Martindale	60000 Rubs
Water penetration After 5 wash 40°C	ISO 811	>1000 No Change
Washing Instructions	Hand wash 40°C, mild detergent	

The test values given are only valid at the point of QC Testing.
The Company reserves the right to alter or amend this specification without prior notice.