




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **3**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	3
Number of Rows	1

Body Features

Primary Product Color	Gray
-----------------------	------

Contact Features

Contact Mating Area Plating Material Thickness	1.524 – 3.048 μm[60 – 120 μin]
Mating Tab Width	.68 mm[.026 in]
PCB Contact Termination Area Plating Material Thickness	1.52 – 3.048 μm
Contact Shape & Form	Square
Contact Layout	Inline
Contact Base Material	Brass



Mating Tab Thickness	.76 mm[.029 in]
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Socket
Contact Current Rating (Max)	5 A

Termination Features

Rectangular Termination Post & Tail Width	.74 mm[.029 in]
Rectangular Termination Post & Tail Thickness	.56 mm[.022 in]
Termination Post & Tail Length	4.3 mm[.169 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Mating Entry Location	Bottom
Housing Material	PBT
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Height	7.6 mm[.3 in]
------------------	---------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

Packaging Features

Packaging Quantity	2800
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1734028-1
Std USB Type A, Plug, Natural




TE Part #281739-6
HEADER HE14 STRAIGHT 2X6 P



TE Part #1007079-1
CONTACT MICROPHONE CM-01



TE Part #825433-2
MOD 2 PINHDR 1X2 P.



TE Part #216024-007
55A0111-26-2



TE Part #2-178128-4
DYNAMIC 3200 REC HSG 4P SGL Y



TE Part #9-1879061-8
CPF0402 110K 0.1% 25PPM 5K RL

Documents

- CAD Files
- 3D PDF



3D

Customer View Model

[ENG_CVM_CVM_163681-1_H_c-163681-1-h.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_163681-1_H_c-163681-1-h.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_163681-1_H_c-163681-1-h.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[CIS Crimp Snap-In Receptacle Contact](#)

English