

DOUBLE RING SPANNER METRIC 30 X 32MM



- Different size at each end to give 2 sizes with one wrench
- Double curved heads offset at 75° for easier use on flat surfaces
- Chrome vanadium satin finish
- TengTools hip grip design for contact with the flat side of the fastening
- Designed and manufactured to DIN 838

Double Ring Spanner 30 x 32mm

General information

Country of origin: Taiwan
Barcode: 5020385041158
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002188
UNSPSC: 27111705

Dimensions

Net weight (g): 627
Length: 362 mm

Attributes

Product type: Double Ring Spanners
Material: CrV
Certificates: N/A
Size: 30 x 32 mm
Tethering facility: No
Spanner type: Regular
Unit of measurement: Metric
Ring diameter (mm): 45.5, 48.5
Ring height (mm): 14.4, 15.2
Offset angle ring (°): 75, 75

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden