



by Schneider Electric


Basic Rack PDU (AP9572)

Overview

The American Power Conversion (APC™) Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The PDU has fifteen (15) IEC-320-C13 outlets.

Power cord. 2.5-m (8.2-ft) IEC-320-C19 to IEC-320-C20 power cord.



Specifications

Electrical

Input connector	IEC-320-C20 plug
Output connectors	fifteen (15) IEC-320-C13 outlets
Nominal input voltage	120 – 230 VAC
Acceptable input voltage	120 – 240 VAC +6%, -10%
Input frequency	50/60 Hz

Physical

Dimensions (H × W × D)	62.00 × 4.44 × 4.44 cm (24.40 × 1.75 × 1.75 in)
Shipping dimensions (H × W × D)	63.81 × 16.82 × 14.60 cm (25.13 × 6.63 × 5.75 in)
Weight	2.00 kg (4.40 lb)
Shipping weight	2.70 kg (6.00 lb)

Environmental

Elevation (above MSL)	
Operating	0 – 3000 m (0 – 10,000 ft)
Storage	0 – 15 000 m (0 – 50,000 ft)
Temperature	
Operating	0 to 45° C (32 to 113° F)
Storage	-25 to 65° C (-13 to 149° F)
Humidity	
Operating	5 – 95% RH, non-condensing
Storage	5 – 95% RH, non-condensing

Compliance

Safety verifications	UL/cUL Listed, CE, VDE, AS/NZS 60950-1
----------------------	---

Customer support and warranty information is available at the APC Web site, www.apc.com.

© 2011 APC by Schneider Electric. All trademarks are owned by Schneider Electric Industries S.A.S., American Power Conversion Corporation, or their affiliated companies.