


Geberit Mapress Stainless Steel bend with plain end (silicone-free)



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	arc °	L cm	H cm	Z cm
80702	12	15	45	2.8	3.6	0.8
80703	15	18	45	2.9	3.6	0.9
80704	20	22	45	3.2	4	1.1
80705	25	28	45	3.7	4.4	1.4

<i>Art. no.</i>	<i>DN</i>	<i>d_ø mm</i>	<i>arc °</i>	<i>L cm</i>	<i>H cm</i>	<i>Z cm</i>
82706	32	35	45	4.3	5	1.7
82707	40	42	45	5.1	5.9	2.1
82708	50	54	45	6.2	7	2.7
82709	65	76.1	45	10.1	11.1	4.8
82710	80	88.9	45	11.7	12.8	5.7
82711	100	108	45	14.3	15.8	6.8
80302	12	15	90	3.8	4.8	1.8
80303	15	18	90	4.2	5.2	2.2
80304	20	22	90	4.7	5.8	2.6
80305	25	28	90	5.7	6.3	3.4
83306	32	35	90	6.8	7.4	4.2
83307	40	42	90	8	8.8	5
83308	50	54	90	10	10.8	6.5

Art. no.	DN	d _ø mm	arc °	L cm	H cm	Z cm
83309	65	76.1	90	15.7	16.7	10.4
83310	80	88.9	90	18.4	19.5	12.4
83311	100	108	90	22.6	24.1	15.1