

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : WYPALL® Cleaning Wipes
Product code : 7772, 7775, 7776

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Cleaning agent

1.3 Details of the supplier of the safety data sheet

Company : Kimberly-Clark Europe Limited
40 London Road
Reigate
Surrey RH2 9QP
United Kingdom
Telephone : +44 1737 736000
Telefax : +44 1737 736670
E-mail address : sdscontact@kcc.com
Responsible/issuing person

1.4 Emergency telephone number

: +44 1865 407333
This telephone number is available 24 hours per day, 7 days per week.

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a dangerous substance according to GHS.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
No labeling elements required.

WYPALL® Cleaning Wipes

Version 1.4 Revision Date: 26.03.2019 SDS Number: 100000001416 Date of last issue: 13.03.2019
Date of first issue: 24.05.2017

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.
No hazards resulting from the material as supplied.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Chemical nature : Solid
Cleaning agent

Hazardous components

Chemical name	CAS-No. EC-No. Registration number	Classification	Concentration (% w/w)
WEL substance :			
Propylene Glycol	57-55-6 200-338-0		>= 2.5 - < 5

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

If inhaled : No hazards which require special first aid measures.

In case of skin contact : No hazards which require special first aid measures.

In case of eye contact : Flush eyes with water as a precaution.
If eye irritation persists, consult a specialist.

If swallowed : Not required under normal use.
Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No information available.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : No hazards which require special first aid measures.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

circumstances and the surrounding environment.

Unsuitable extinguishing media : No information available.

5.2 Special hazards arising from the substance or mixture

Specific hazards during firefighting : No information available.

Hazardous combustion products : Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Product contains a high percentage of water.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Material can create slippery conditions.

6.2 Environmental precautions

Environmental precautions : No special environmental precautions required.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : No special handling advice required.

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place.

Advice on common storage : No special restrictions on storage with other products.

WYPALL® Cleaning Wipes

Version 1.4 Revision Date: 26.03.2019 SDS Number: 100000001416 Date of last issue: 13.03.2019
Date of first issue: 24.05.2017

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Skin-care

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Propylene Glycol	57-55-6	TWA (particles)	10 mg/m ³	GB EH40
Further information	Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used			
		TWA (Total vapour and particles)	150 ppm 474 mg/m ³	GB EH40
Further information	Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used			

8.2 Exposure controls

Engineering measures

none

Personal protective equipment

Eye protection : Not required under normal use.

Hand protection

Remarks : not required under normal use

Skin and body protection : Not required under normal use.

Respiratory protection : Not required under normal use.

Protective measures : No special protective equipment required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : No data available

Colour : white

Odour : pleasant

Odour Threshold : No data available

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

WYPALL® Cleaning Wipes

Version 1.4	Revision Date: 26.03.2019	SDS Number: 100000001416	Date of last issue: 13.03.2019 Date of first issue: 24.05.2017
----------------	------------------------------	-----------------------------	---

pH	:	5.0 - 7.0
Melting point/range	:	< -2 °C
Boiling point/boiling range	:	No data available
Flash point	:	> 70 °C
Evaporation rate	:	No data available
Flammability (solid, gas)	:	Not classified as a flammability hazard
Upper explosion limit	:	Not applicable
Lower explosion limit	:	Not applicable
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Density	:	0.996 - 1.010 g/cm ³
Solubility(ies)		
Solubility in other solvents	:	insoluble
Partition coefficient: n-octanol/water	:	Not applicable
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity		
Viscosity, kinematic	:	Not applicable
Explosive properties	:	No data available
Oxidizing properties	:	No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Stable under recommended storage conditions.

10.2 Chemical stability

No decomposition if stored and applied as directed.

10.3 Possibility of hazardous reactions

Hazardous reactions : No hazards to be specially mentioned.

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : None.

10.6 Hazardous decomposition products

Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Information on likely routes of exposure : Skin contact

Acute toxicity

Components:

Propylene Glycol:

Acute oral toxicity : LD50 Oral (Rat, male and female): 22,000 mg/kg
Method: Acute toxicity estimate
GLP: no

Acute inhalation toxicity : LC50 (Rabbit): > 317,042 mg/m³
Exposure time: 2 h
Method: No information available.
GLP: no

Acute dermal toxicity : LD50 Dermal (Rabbit): > 2,000 mg/kg
Method: No information available.
GLP: no

Skin corrosion/irritation

Product:

Remarks: According to the classification criteria of the European Union, the product is not considered as being a skin irritant.

Components:

Propylene Glycol:

Species: Rabbit
Method: OECD Test Guideline 404
Result: No skin irritation
GLP: No information available.

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

Serious eye damage/eye irritation

Product:

Remarks: According to the classification criteria of the European Union, the product is not considered as being an eye irritant.

Components:

Propylene Glycol:

Species: Rabbit
Method: OECD Test Guideline 405
Result: No eye irritation
GLP: No information available.

Respiratory or skin sensitisation

Product:

Remarks: Based on available data, the classification criteria are not met.

Components:

Propylene Glycol:

Test Type: Maximisation Test
Species: Guinea pig
Method: OECD Test Guideline 406
Result: Did not cause sensitisation on laboratory animals.
GLP: No information available.

Germ cell mutagenicity

Product:

Germ cell mutagenicity-
Assessment : Contains no ingredient listed as a mutagen

Carcinogenicity

Product:

Carcinogenicity -
Assessment : Contains no ingredient listed as a carcinogen

Reproductive toxicity

Product:

Reproductive toxicity -
Assessment : Contains no ingredient listed as toxic to reproduction

STOT - single exposure

Product:

Remarks: No data available

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

STOT - repeated exposure

Product:

Remarks: No data available

Aspiration toxicity

Product:

No aspiration toxicity classification

Further information

Product:

Remarks: The product contains no substances which at their given concentration, are considered to be hazardous to health.

SECTION 12: Ecological information

12.1 Toxicity

Product:

Toxicity to fish : Remarks: No data available

Components:

Propylene Glycol:

Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): 40,613 mg/l
Exposure time: 96 h
Test Type: static test
Method: No information available.
GLP: no

Toxicity to daphnia and other aquatic invertebrates : EC50 (Americamysis): 18,800 mg/l
Exposure time: 96 h
Test Type: static test
Method: No information available.
GLP: yes

Toxicity to algae : EC50 (Pseudokirchneriella subcapitata (green algae)): 24,200 mg/l
Exposure time: 72 h
Test Type: static test
Method: OECD Test Guideline 201
GLP: yes

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC: 13,020 mg/l
Exposure time: 7 d

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

12.2 Persistence and degradability

Product:

Biodegradability : Remarks: No information available.

12.3 Bioaccumulative potential

Product:

Bioaccumulation : Remarks: No data available

12.4 Mobility in soil

Product:

Distribution among environmental compartments : Remarks: No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..
Remarks: Based on available data, the classification criteria are not met.

12.6 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Directive 96/82/EC does not apply

15.2 Chemical safety assessment

No information available.

SECTION 16: Other information

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship;

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

WYPALL® Cleaning Wipes

Version	Revision Date:	SDS Number:	Date of last issue: 13.03.2019
1.4	26.03.2019	100000001416	Date of first issue: 24.05.2017

REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN