

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- 1.1.

Product identifier

Isopropyl Alcohol Liquid

Substance / mixture

mixture

Product codes

315454, 652745

UFI

U9G0-Y0H0-P001-4J0P
- 1.2.

Relevant identified uses of the substance or mixture and uses advised against

Mixture's intended use

Cleaning agent.

Mixture uses advised against

The product should not be used in ways other than those referred in Section 1.
- 1.3.

Details of the supplier of the safety data sheet

Manufacturer

RS Components Ltd

Birchington Road

Corby

Northants

NN17 9RS

Tel: +44 (0) 845 850 9900

RCustomerServicesUK@rs-components.com

RS Components Ltd

Glenview Industrial Estate

Herberton Road

Rialto

Dublin 12

Tel: +353 (0) 1 415 3100

enquiries.ie@rs-components.com
- 1.4.

Emergency telephone number

Tel: +44 (0) 1865 407333 (24hr)

GB: N/A

+44 1235 239670 (24hr)

IE: +353 (0)1 809 2166 (08:00 - 22:00)

SECTION 2: Hazards identification

- 2.1.

Classification of the substance or mixture

Classification of the mixture in accordance with Regulation (EC) No 1272/2008

The mixture is classified as dangerous.

Flam. Liq. 2, H225

Eye Irrit. 2, H319

STOT SE 3, H336

Most serious adverse physico-chemical effects

Highly flammable liquid and vapour.

Most serious adverse effects on human health and the environment

May cause drowsiness or dizziness. Causes serious eye irritation.
- 2.2.

Label elements

Hazard pictogram



SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

Signal word

Danger

Hazardous substances

propan-2-ol

Hazard statements

H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Precautionary statements

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P264 Wash face, hands and exposed parts of the body thoroughly after handling.
P271 Use only outdoors or in a well-ventilated area.
P280 Wear protective gloves/eye protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 If eye irritation persists: Get medical advice/attention.
P405 Store locked up.
P501 Dispose of container to in accordance with local/regional/national/international regulations.

Requirements for child-resistant fastenings and tactile warning of danger

Container must carry a tactile warning of danger.

2.3. Other hazards

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605. Mixture does not contain any substance meet the criteria for PBT or vPvB in accordance with Annex XIII of Regulation (EC) No. 1907/2006 (REACH) as amended.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Mixture contains these hazardous substances and substances with the highest permissible concentration in the working environment

Identification numbers	Substance name	Content in % weight	Classification according to Regulation (EC) No 1272/2008	Note
Index: 603-117-00-0 CAS: 67-63-0 EC: 200-661-7	propan-2-ol	>50	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336	

Full text of all classifications and hazard statements is given in the section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Take care of your own safety. If any health problems are manifested or if in doubt, inform a doctor and show him information from this safety data sheet. If unconscious, put the person in the stabilized (recovery) position on his side with his head slightly bent backwards and make sure that airways are free; never induce vomiting. If the person vomits by himself, make sure that the vomit is not inhaled. In life threatening conditions first of all provide resuscitation of the affected person and ensure medical assistance. Respiratory arrest - provide artificial respiration immediately. Cardiac arrest - provide indirect cardiac massage immediately.

If inhaled

Terminate the exposure immediately; move the affected person to fresh air. Protect the person against growing cold. Provide medical treatment if irritation, dyspnoea or other symptoms persist.

If on skin

Remove contaminated clothes. Wash the affected area with plenty of water, lukewarm if possible. Soap, soap solution or shampoo should be used if there is no skin injury. Provide medical treatment if skin irritation persists. Rinse skin with water or shower.

If in eyes

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

Rinse eyes immediately with a flow of running water, open the eyelids (also using force if needed); remove contact lenses immediately if worn by the affected person. Rinsing should continue at least for 10 minutes. Provide medical treatment, specialized if possible.

If swallowed

Rinse out the mouth with water and provide 2-5 dL of water. Provide medical treatment if the person has any health problems.

4.2. Most important symptoms and effects, both acute and delayed

If inhaled

May cause drowsiness or dizziness.

If on skin

Not expected.

If in eyes

Causes serious eye irritation.

If swallowed

Irritation, nausea.

4.3. Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam, carbon dioxide, powder, water spray jet, water mist.

Unsuitable extinguishing media

Water - full jet.

5.2. Special hazards arising from the substance or mixture

In the event of fire, carbon monoxide, carbon dioxide and other toxic gases may arise. Inhalation of hazardous degradation (pyrolysis) products may cause serious health damage.

5.3. Advice for firefighters

Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely. Use a self-contained breathing apparatus and full-body protective clothing. Closed containers with the product near the fire should be cooled with water. Do not allow run-off of contaminated fire extinguishing material to enter drains or surface and ground water.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Provide sufficient ventilation. Highly flammable liquid and vapour. Remove all ignition sources. Use personal protective equipment for work. Follow the instructions in the Sections 7 and 8. Do not inhale mist/vapours/spray. Prevent contact with skin and eyes.

6.2. Environmental precautions

Prevent contamination of the soil and entering surface or ground water.

6.3. Methods and material for containment and cleaning up

Spilled product should be covered with suitable (non-flammable) absorbing material (sand, diatomaceous earth, earth and other suitable absorption materials); to be contained in well closed containers and removed as per the Section 13. In the event of leakage of the substantial amount of the product, inform fire brigade and other competent bodies. After removal of the product, wash the contaminated site with plenty of water. Do not use solvents.

6.4. Reference to other sections

See the Section 7, 8 and 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Prevent formation of gases and vapours in flammable or explosive concentrations. The product should be used only in the areas where it is not in contact with open fire and other ignition sources. Use non-sparking tools. Use of antistatic clothes and footwear is recommended. Do not inhale mist/vapours/spray. Prevent contact with skin and eyes. No smoking. Wash hands and exposed parts of the body thoroughly after handling. Use only outdoors or in a well-ventilated area. Use personal protective equipment as per Section 8. Observe valid legal regulations on safety and health protection. Ground and bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting equipment. Take action to prevent static discharges.

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

- 7.2.

Conditions for safe storage, including any incompatibilities

Store in tightly closed containers in cold, dry and well ventilated areas designated for this purpose. Do not expose to sunlight. Store locked up. Keep container tightly closed. Keep cool.
- The specific requirements or rules relating to the substance/mixture

Solvent vapours are heavier than air and accumulate especially near the floor where they may form an explosive mixture with the air.
- 7.3.

Specific end use(s)

not available

SECTION 8: Exposure controls/personal protection

- 8.1.

Control parameters

The mixture contains no substances for which occupational exposure limits are set.
- 8.2.

Exposure controls

Follow the usual measures intended for health protection at work and especially for good ventilation. This can be achieved only by local suction or efficient general ventilation. If exposure limits cannot be observed in this mode, suitable protection of airways must be used. Do not eat, drink and smoke during work. Wash your hands thoroughly with water and soap after work and before breaks for a meal and rest.

Eye/face protection

Protective goggles.

Skin protection

Hand protection: Protective gloves resistant to the product. Contaminated skin should be washed thoroughly.

Respiratory protection

Halfmask with a filter against organic vapours in the poorly ventilated environment.

Thermal hazard

Not available.

Environmental exposure controls

Observe usual measures for protection of the environment, see Section 6.2.
- SECTION 9: Physical and chemical properties
- 9.1.

Information on basic physical and chemical properties

Physical state	liquid
Colour	colourless
Odour	containing alcohol
Melting point/freezing point	-114 °C
Boiling point or initial boiling point and boiling range	78 °C
Flammability	data not available
Lower and upper explosion limit	
bottom	15 %
upper	19 %
Flash point	11.7 °C
Auto-ignition temperature	data not available
Decomposition temperature	data not available
pH	6.5-7.5 (undiluted)
Kinematic viscosity	data not available
Solubility in water	data not available
Partition coefficient n-octanol/water (log value)	data not available
Vapour pressure	data not available
Density and/or relative density	data not available
Relative vapour density	data not available
Particle characteristics	data not available

9.2.

Other information

not available

9.2.1.

Information on test results

not available
- Page 4/8

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

9.2.2. Information on mixture
not available

SECTION 10: Stability and reactivity

- 10.1. Reactivity
not available
- 10.2. Chemical stability
The product is stable under normal conditions.
- 10.3. Possibility of hazardous reactions
Unknown.
- 10.4. Conditions to avoid
The product is stable and no degradation occurs under normal use. Protect against flames, sparks, overheating and against frost.
- 10.5. Incompatible materials
Protect against strong acids, bases and oxidizing agents.
- 10.6. Hazardous decomposition products
Not developed under normal uses. Dangerous outcomes such as carbon monoxide and carbon dioxide are formed at high temperature and in fire.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008
No toxicological data is available for the mixture.

Acute toxicity
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Skin corrosion/irritation
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Serious eye damage/irritation
Causes serious eye irritation. Data for the components of the mixture are not available.

Respiratory or skin sensitisation
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Germ cell mutagenicity
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Carcinogenicity
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Reproductive toxicity
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Toxicity for specific target organ - single exposure
May cause drowsiness or dizziness. Data for the components of the mixture are not available.

Toxicity for specific target organ - repeated exposure
No data are available for either the mixture or the components. Based on the available data, the criteria for

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

classification of the mixture are not met.

Aspiration hazard

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

11.2. Information on other hazards

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

SECTION 12: Ecological information

12.1. Toxicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

12.2. Persistence and degradability

No data are available for either the mixture or the components.

12.3. Bioaccumulative potential

No data are available for either the mixture or the components.

12.4. Mobility in soil

No data are available for either the mixture or the components.

12.5. Results of PBT and vPvB assessment

Product does not contain any substance meeting the criteria for PBT or vPvB in accordance with the Annex XIII of Regulation (EC) No 1907/2006 (REACH) as amended.

12.6. Endocrine disrupting properties

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

12.7. Other adverse effects

Not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Hazard of environmental contamination; dispose of the waste in accordance with the local and/or national regulations. Proceed in accordance with valid regulations on waste disposal. Any unused product and contaminated packaging should be put in labelled containers for waste collection and submitted for disposal to a person authorised for waste removal (a specialized company) that is entitled for such activity. Do not empty unused product in drainage systems. The product must not be disposed of with municipal waste. Empty containers may be used at waste incinerators to produce energy or deposited in a dump with appropriate classification. Perfectly cleaned containers can be submitted for recycling.

Waste management legislation

Directive 2008/98/EC of the European Parliament and of the Council of 19 November 2008 on waste, as amended. Decision 2000/532/EC establishing a list of wastes, as amended.

SECTION 14: Transport information

14.1. UN number or ID number

UN 1219

14.2. UN proper shipping name

ISOPROPANOL

14.3. Transport hazard class(es)

3 Flammable liquids

14.4. Packing group

II

14.5. Environmental hazards

not relevant

14.6. Special precautions for user

Reference in the Sections 4 to 8.

14.7. Maritime transport in bulk according to IMO instruments

not relevant

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024	Version	3.0
Revision date	12th June 2024		

Additional information

Hazard identification No.	33
UN number	1219
Classification code	F1
Safety signs	3



Tunnel restriction code	(D/E)
-------------------------	-------

Air transport - ICAO/IATA

Packaging instructions passenger	353
Cargo packaging instructions	364

Marine transport - IMDG

EmS (emergency plan)	F-E, S-D
MFAG	305

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18th December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing the European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No. 793/93 and Commission Regulation (EC) No. 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, as amended. REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Commission Regulation (EU) 2020/878 of 18 June 2020 amending Annex II to Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

National regulations (Germany)
WGK Water hazard class: WGK 1 - slightly hazardous to water

15.2. Chemical safety assessment

not available

SECTION 16: Other information

A list of standard risk phrases used in the safety data sheet

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Guidelines for safe handling used in the safety data sheet

P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P264	Wash face, hands and exposed parts of the body thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves/eye protection.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313	If eye irritation persists: Get medical advice/attention.
P405	Store locked up.
P501	Dispose of container to in accordance with local/regional/national/international regulations.

Other important information about human health protection

The product must not be - unless specifically approved by the manufacturer/importer - used for purposes other than as per the Section 1. The user is responsible for adherence to all related health protection regulations.

Key to abbreviations and acronyms used in the safety data sheet

ADR European agreement concerning the international carriage of dangerous goods by

SAFETY DATA SHEET			
according to Commission Regulation (EU) 2020/878 as amended			
Isopropyl Alcohol Liquid			
Creation date	10th May 2024		
Revision date	12th June 2024	Version	3.0

	road
BCF	Bioconcentration Factor
CAS	Chemical Abstracts Service
CLP	Regulation (EC) No 1272/2008 on classification, labelling and packaging of substance and mixtures
EC	Identification code for each substance listed in EINECS
EINECS	European Inventory of Existing Commercial Chemical Substances
EmS	Emergency plan
EU	European Union
EuPCS	European Product Categorisation System
IATA	International Air Transport Association
IBC	International Code For The Construction And Equipment of Ships Carrying Dangerous Chemicals
ICAO	International Civil Aviation Organization
IMDG	International Maritime Dangerous Goods
IMO	International Maritime Organization
INCI	International Nomenclature of Cosmetic Ingredients
ISO	International Organization for Standardization
IUPAC	International Union of Pure and Applied Chemistry
log Kow	Octanol-water partition coefficient
OEL	Occupational Exposure Limits
PBT	Persistent, Bioaccumulative and Toxic
ppm	Parts per million
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals
RID	Agreement on the transport of dangerous goods by rail
UN	Four-figure identification number of the substance or article taken from the UN Model Regulations
UVCB	Substances of unknown or variable composition, complex reaction products or biological materials
VOC	Volatile organic compounds
vPvB	Very Persistent and very Bioaccumulative
Eye Irrit.	Eye irritation
Flam. Liq.	Flammable liquid
STOT SE	Specific target organ toxicity - single exposure

Training guidelines

Inform the personnel about the recommended ways of use, mandatory protective equipment, first aid and prohibited ways of handling the product.

Recommended restrictions of use

not available

Information about data sources used to compile the Safety Data Sheet

REGULATION (EC) No. 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL (REACH) as amended.
REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Data from the manufacturer of the substance / mixture, if available - information from registration dossiers.

More information

Classification procedure - calculation method.

Statement

The safety data sheet provides information aimed at ensuring safety and health protection at work and environmental protection. The provided information corresponds to the current status of knowledge and experience and complies with valid legal regulations. The information should not be understood as guaranteeing the suitability and usability of the product for a particular application.