

Siemens
EcoTech



solid-state contactor 1-pole 3RF33 AC-1 30 A 40 °C / 48-460 V / 24 V AC/DC / screw terminal



product brand name	SIRIUS
product designation	solid-state contactor
product type designation	3RF33
manufacturer's article number	
• _1 of the accessories that can be ordered	3RF2900-3PA88
• _3 of the accessories that can be ordered	3RF3900-0EA18
• _4 of the accessories that can be ordered	3RF3950-0GA16
product designation	
• _1 of the accessories that can be ordered	terminal cover
• _3 of the accessories that can be ordered	converter
• _4 of the accessories that can be ordered	load monitoring
General technical data	
product function	zero-point switching
power loss [V·A] maximum	25 VA
power loss [W] for rated value of the current	
• at AC in hot operating state	27 W
• at AC in hot operating state per pole	27 W
• without load current share typical	0.5 W
type of calculation of power loss current-dependent	linear
insulation voltage rated value	600 V
degree of pollution	3
surge voltage resistance of main circuit rated value	6 kV
protection class IP	IP20
protection class IP on the front according to IEC 60529	IP20
shock resistance according to IEC 60068-2-27	15 g / 11 ms
vibration resistance according to IEC 60068-2-6	2 g
reference code according to IEC 81346-2	Q
Substance Prohibitance (day/month/year)	01/15/2024
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 Dibutylbis(pentane-2,4-dionato-O,O')tin CAS-No. 22673-19-4
Net Weight	0.165 kg
Main circuit	
number of poles for main current circuit	1

number of NO contacts for main contacts	1
number of NC contacts for main contacts	0
type of voltage of the operating voltage	AC
operating voltage - at AC - at 50 Hz rated value - at 60 Hz rated value	48 ... 460 V 48 ... 460 V
operating frequency rated value	50 ... 60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operating range relative to the operating voltage at AC - at 50 Hz - at 60 Hz	40 ... 506 V 40 ... 506 V
operational current rated value maximum	30 A
operational current - at AC-1 at 400 V rated value - at AC-51 rated value - at AC-51 according to IEC 60947-4-3 - according to UL 508 rated value	30 A 30 A 30 A 24 A
ampacity maximum	30 A
operational current minimum	500 mA
rate of voltage rise at the thyristor for main contacts maximum permissible	1 000 V/μs
blocking voltage at the thyristor for main contacts maximum permissible	1 200 V
reverse current of the thyristor	10 mA
derating temperature	40 °C
surge current resistance rated value	1 300 A
I ² t value maximum	8 000 A ² ·s
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC - at 50 Hz - at 60 Hz	14 ... 27 V 14 ... 27 V
control supply voltage 1 at AC - at 50 Hz rated value - at 60 Hz rated value	24 V 24 V
control supply voltage at AC - at 50 Hz full-scale value for signal<0> recognition - at 60 Hz full-scale value for signal<0> recognition - initial value for signal <1> detection	5 V 5 V 14 V
control supply voltage frequency 1 rated value 2 rated value	50 Hz 60 Hz
control supply voltage at DC	15 ... 24 V
control supply voltage 1 at DC rated value	24 V
control supply voltage at DC - initial value for signal <1> detection - full-scale value for signal<0> recognition	15 V 5 V
symmetrical line frequency tolerance	5 Hz
operating range factor control supply voltage rated value at DC - initial value - full-scale value	0.63 1.25
operating range factor control supply voltage rated value at AC at 50 Hz - initial value - full-scale value	0.58 1.13
operating range factor control supply voltage rated value at AC at 60 Hz initial value	0.58

• full-scale value	1.13
control current at minimum control supply voltage	
• at AC	2 mA
control current at AC rated value	15 mA
control current at DC rated value	20 mA
ON-delay time	1 ms; additionally max. one half-wave
OFF-delay time	15 ms; additionally max. one half-wave
Installation/ mounting/ dimensions	
fastening method side-by-side mounting	Yes
fastening method	screw fixing and snap-on mounting on standard mounting rail 35 mm according to IEC 60715
design of the thread of the screw for securing the equipment	M4
height	95 mm
width	22.5 mm
depth	121 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	
• for main current circuit	screw-type terminals
• for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
• for main contacts	
— solid	2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²)
— finely stranded with core end processing	2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²), 1x 10 mm ²
• for AWG cables for main contacts	2x (14 ... 10), 1x 8
connectable conductor cross-section for main contacts	
• solid or stranded	1.5 ... 6 mm ²
• finely stranded with core end processing	1 ... 10 mm ²
type of connectable conductor cross-sections	
• for auxiliary and control contacts	
— solid	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
— finely stranded with core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
— finely stranded without core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
• for AWG cables for auxiliary and control contacts	1x (20 ... 12)
AWG number as coded connectable conductor cross section for main contacts	14 ... 8
tightening torque	
• for main contacts with screw-type terminals	2 ... 2.5 N·m
• for auxiliary and control contacts with screw-type terminals	0.5 ... 0.6 N·m
tightening torque [lbf·in]	
• for main contacts with screw-type terminals	18 ... 22 lbf·in
• for auxiliary and control contacts with screw-type terminals	4.5 ... 5.3 lbf·in
design of the thread of the connection screw	
• for main contacts	M4
• of the auxiliary and control contacts	M3
stripped length of the cable	
• for main contacts	10 mm
• for auxiliary and control contacts	7 mm
type of grounding	grounding by snapping onto grounded DIN rails
UL/CSA ratings	
operational current according to UL 508 rated value	24 A
Electrical Safety	
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Ambient conditions	
installation altitude at height above sea level maximum	1 000 m
ambient temperature	

- during operation - during storage	-25 ... +60 °C -55 ... +80 °C		
Electromagnetic compatibility			
conducted interference - due to burst according to IEC 61000-4-4 - due to conductor-earth surge according to IEC 61000-4-5 - due to conductor-conductor surge according to IEC 61000-4-5 - due to high-frequency radiation according to IEC 61000-4-6	2 kV / 5 kHz, behavior criterion 2 2 kV, behavior criterion 2 1 kV, behavior criterion 2 140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1		
field-based interference according to IEC 61000-4-3	80 MHz ... 1 GHz 10 V/m, behavior criterion 1		
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging / 8 kV air discharging, behavior criterion 2		
conducted HF interference emissions according to CISPR11	Class A for industrial environment		
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments		
Short-circuit protection, design of the fuse link			
manufacturer's article number - of full range R fuse link for semiconductor protection at NH design usable - of gS fuse for semiconductor protection at NH design usable - of full range R fuse link for semiconductor protection at cylindrical design usable - of back-up R fuse link for semiconductor protection at NH design usable - of back-up R fuse link for semiconductor protection at cylindrical design 10 x 38 mm usable - of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable - of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable	3NE8702-1 3NE1803-0 5SE1335 3NE8801-0MK 3NC1032 3NC1450 3NC2263		
manufacturer's article number of the gG fuse - at NH design usable - at NH design usable note - at cylindrical design 10 x 38 mm usable - at cylindrical design 14 x 51 mm usable - at cylindrical design 22 x 58 mm usable	3NA6807: These fuses have a smaller rated current than the semiconductor relays These fuses have a smaller rated current than the semiconductor relays 3NW6012-1 3NW6112-1 3NW6212-1		
manufacturer's article number - of DIAZED fuse usable - of NEOZED fuse usable	5SB4011 5SE2335		
Approvals Certificates			
Environment	General Product Approval		
Environmental Confirmations	    		
EMV	Test Certificates	other	
 RCM	Type Test Certificates/Test Report	Confirmation 	Confirmation
Further information			
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012 Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10			

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF3330-1AA14>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF3330-1AA14>




Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RF3330-1AA14>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF3330-1AA14&lang=en





last modified:

7/16/2026