

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name: MAINTAIN SCREENWASH

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Cleaning agent

Uses advised against: No uses advised against identified.

1.3 Details of the supplier of the safety data sheet

Manufacturer / Supplier FUCHS LUBRICANTS (UK) PLC.

New Century Street

ST1 5HU Hanley

Telephone: +44 (0) 1782 203700

Contact Person: Product Safety department

E-mail: product.safety@fuchs.com

Telephone: +44 (0) 1782 203700

1.4 Emergency telephone number: UK NHS: Dial 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

|| The product has been classified and labelled as hazardous according to regulation GB-CLP.

Classification according to GB-CLP.

Physical Hazards

Flammable liquids

Category 3

H226: Flammable liquid and vapor.

Hazard summary

Physical Hazards: No data available.

2.2 Label Elements



||Signal Words: Warning

Product name: MAINTAIN SCREENWASH

Hazard Statement(s): H226: Flammable liquid and vapor.

Precautionary Statements

Prevention: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

2.3 Other hazards: By handling of mineral oil products and chemical products no particular hazard is known when normal precautions (item 7) and personal protective equipment (item 8) are kept.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

General information: Mixture of the substances listed below with harmless additions. This product is applied only as solution or emulsion in water.

Chemical name	Identifier	Concentration *	UK-REACH Registration No.	Notes
Ethanol	EINECS: 200-578-6	20,00% - <50,00%		
Isopropyl alcohol	EINECS: 200-661-7	1,00% - <5,00%		
Propylene glycol	EINECS: 200-338-0	1,00% - <5,00%		

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

Classification

Chemical name	Identifier	Classification
Ethanol	EINECS: 200-578-6	GBCLP: Flam. Liq. 2;H225, Eye Irrit. 2;H319
Isopropyl alcohol	EINECS: 200-661-7	GBCLP: Flam. Liq. 2;H225, Eye Irrit. 2;H319, STOT SE 3;H336
Propylene glycol	EINECS: 200-338-0	GBCLP:

GB-CLP

specific concentration limit

Chemical name	Identifier	specific concentration limit	Hazard class	Hazard Category	Hazard statements
Ethanol	EINECS: 200-578-6	>= 50 %	Serious eye irritation	2	H319

For the wording of the listed hazard statements refer to section 16.

SECTION 4: First aid measures

General: Instantly remove any clothing soiled by the product.

4.1 Description of first aid measures

Product name: MAINTAIN SCREENWASH

Inhalation:	Supply fresh air; consult doctor in case of symptoms.
Eye contact:	Promptly wash eyes with plenty of water while lifting the eye lids.
Skin Contact:	Wash with soap and water.
Ingestion:	Rinse mouth thoroughly.
4.2 Most important symptoms and effects, both acute and delayed:	May cause skin and eye irritation.
4.3 Indication of any immediate medical attention and special treatment needed	Get medical attention if symptoms occur.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media:	CO ₂ , fire extinguishing powder or fog like water spraying. Extinguish larger fires with alcohol resistant foam or spray water with suitable surfactant added
Unsuitable extinguishing media:	Water with a full water jet.

5.2 Special hazards arising from the substance or mixture:

During fire, gases hazardous to health may be formed.

5.3 Advice for firefighters

Special fire-fighting procedures:	Move container from fire area if it can be done without risk. Dispose of fire debris and contaminated fire fighting water in accordance with official regulations. Collect contaminated fire fighting water separately. It must not enter drains.
Special protective equipment for fire-fighters:	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures:

In case of spills, beware of slippery floors and surfaces. Keep away from sources of ignition - No smoking.

6.2 Environmental Precautions:

Prevent from spreading (e.g. by binding or oil barriers). Avoid release to the environment. Environmental manager must be informed of all major spillages. Prevent further leakage or spillage if safe to do so. Do not allow to enter drainage system, surface or ground water.

Product name: MAINTAIN SCREENWASH

6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acidbinders, universal binders, sawdust). Dispose of the material collected according to regulations. Stop the flow of material, if this is without risk.

6.4 Reference to other sections:

See Section 8 of the SDS for Personal Protective Equipment. See Section 7 for information on safe handling See Section 13 for information on disposal.

SECTION 7: Handling and storage:

7.1 Precautions for safe handling:

Prevent formation of aerosols. Do not eat, drink or smoke when working with the product. Take usual precautions when handling mineral oil products or chemical products. Observe good industrial hygiene practices. Provide adequate ventilation.

7.2 Conditions for safe storage, including any incompatibilities:

Store in original tightly closed container. Keep separate from food, feedstuffs, fertilizers and other sensitive material. Store away from incompatible materials. No special precautions necessary if used correctly. Use only containers specifically permitted for this substance/product. Protect from contamination

7.3 Specific end use(s):

Not applicable

Storage Class:

10, Combustible liquids

SECTION 8: Exposure controls/personal protection

8.1 Control Parameters

Occupational Exposure Limits

Chemical name	Type	Exposure Limit Values	Source
Ethanol	TWA	1.000 ppm 1.920 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)
Isopropyl alcohol	TWA	400 ppm 999 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)
Isopropyl alcohol	STEL	500 ppm 1.250 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)
Propylene glycol - Particulate.	TWA	10 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)
Propylene glycol - Total vapour and particulates.	TWA	150 ppm 474 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)

8.2 Exposure controls

Appropriate engineering controls:

Provide adequate ventilation. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Product name: MAINTAIN SCREENWASH

General information:	Wash hands before breaks and after work. Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. The usual precautionary measures should be adhered to in handling the chemicals or the mineral oil products.
Eye/face protection:	Safety glasses (EN 166) recommended during refilling. Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield.
Skin protection	
Hand Protection:	Material: Nitrile butyl rubber (NBR). Min. Breakthrough time: ≥ 480 min Recommended thickness of the material: $\geq 0,38$ mm Avoid long-term and repeated skin contact. Suitable gloves can be recommended by the glove supplier. Use skin protection cream for preventive skin protection. Protective gloves, where permitted in acc. to safety directions. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
Other:	Do not carry cleaning cloths impregnated with the product in trouser pockets. Wear suitable protective clothing.
Respiratory Protection:	Ensure good ventilation/exhaustion at the workplace. Avoid breathing vapour/ aerosol.
Thermal hazards:	Not known.
Hygiene measures:	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.
Environmental Controls:	No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties**Appearance**

Physical state:	liquid
Form:	liquid
Color:	Blue
Odor:	Characteristic
pH:	8,0 (100 %)
Freezing point:	not determined
Boiling Point:	> 35 °C
Flash Point:	32 °C
Evaporation Rate:	Not applicable for mixtures
Flammability (solid, gas):	not determined

Product name: MAINTAIN SCREENWASH

Flammability Limit - Upper (%)—:	Not applicable for mixtures
Flammability Limit - Lower (%)—:	Not applicable for mixtures
Vapor pressure:	Not applicable for mixtures
Relative vapor density:	Not applicable for mixtures
Density:	0,95 g/cm ³ (15 °C)
Solubility(ies)	
Solubility in Water:	Soluble
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	Not applicable for mixtures
Autoignition Temperature:	not determined
Decomposition Temperature:	not determined
Flow time	Value not relevant for classification
Explosive properties:	Value not relevant for classification
Oxidizing properties:	Value not relevant for classification
Particle characteristics:	Not applicable

9.2 Other information

Minimum ignition temperature:	> 100 °C
--------------------------------------	----------

SECTION 10: Stability and reactivity

10.1 Reactivity:	Stable under normal use conditions.
10.2 Chemical Stability:	Stable under normal use conditions.
10.3 Possibility of hazardous reactions:	Stable under normal use conditions.
10.4 Conditions to avoid:	Stable under normal use conditions.
10.5 Incompatible Materials:	Strong oxidizing substances. Strong acids. Strong bases.
10.6 Hazardous Decomposition Products:	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Oral

Product:	Not classified for acute toxicity based on available data.
-----------------	--

Product name: MAINTAIN SCREENWASH

Specified substance(s)

Ethanol	LD 50 (Rat): > 6.200 mg/kg
Isopropyl alcohol	LD 50 (Rat): 4.570 mg/kg
Propylene glycol	LD 50 (Rat): > 5.000 mg/kg

Dermal

Product: Not classified for acute toxicity based on available data.

Specified substance(s)

Ethanol	LD 50 (Rabbit): > 20.000 mg/kg (OECD 402)
Isopropyl alcohol	LD 50 (Rabbit): 13.400 mg/kg
Propylene glycol	LD 50 (Rabbit): > 10.000 mg/kg

Inhalation

Product: Not classified for acute toxicity based on available data.

Specified substance(s)

Isopropyl alcohol	LC 50 (Rat, 4 h): 30 mg/l
-------------------	---------------------------

Skin Corrosion/Irritation:

Product: Based on available data, the classification criteria are not met.

Serious Eye Damage/Eye Irritation:

Product: Based on available data, the classification criteria are not met.

Respiratory or Skin Sensitization:

Product: Skin sensitizer: Based on available data, the classification criteria are not met.
Respiratory sensitizer: Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity

Product: Based on available data, the classification criteria are not met.

Carcinogenicity

Product: Based on available data, the classification criteria are not met.

Reproductive toxicity

Product: Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Product: Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Repeated Exposure

Product: Based on available data, the classification criteria are not met.

Aspiration Hazard

Product: Based on available data, the classification criteria are not met.

Other adverse effects:

No data available.

Product name: MAINTAIN SCREENWASH

SECTION 12: Ecological information

General information: Not applicable

12.1 Toxicity

Acute toxicity

Product: Based on available data, the classification criteria are not met.

Fish

Specified substance(s)

Ethanol LC 50 (Fish, 96 h): > 2.000 mg/l (OECD 203)

Isopropyl alcohol LC 50 (Fish, 96 h): 9.640 mg/l

Propylene glycol LC 50 (Fish, 96 h): > 500 mg/l

Aquatic Invertebrates

Specified substance(s)

Ethanol LC 50 (Water Flea, 48 h): 5.012 mg/l

Isopropyl alcohol LC 50 (48 h): 1.400 mg/l

Chronic Toxicity

Product: Based on available data, the classification criteria are not met.

Aquatic Invertebrates

Specified substance(s)

Ethanol NOEC (Water Flea, 10 d): 9,6 mg/l

Toxicity to Aquatic Plants

Specified substance(s)

Ethanol EC 50 (Alga, 72 h): 275 mg/l (OECD 201)

NOEC (Alga, 7 d): 208 mg/l (OECD 201)

Isopropyl alcohol LC 50 (Alga, 72 h): > 100 mg/l

12.2 Persistence and Degradability

Biodegradation

Product: Not applicable for mixtures

Specified substance(s)

Ethanol > 70 % (5 d, OECD 301D) Readily biodegradable

Propylene glycol Readily biodegradable

12.3 Bioaccumulative potential

Product: Not applicable for mixtures

12.4 Mobility in soil:

Product: Not applicable for mixtures

Product name: MAINTAIN SCREENWASH

12.5 Results of PBT and vPvB assessment: The product does not contain any substances fulfilling the PBT/vPvB criteria.

12.6 Other adverse effects: None.

Water Hazard Class (WGK): WGK 1: slightly water-endangering.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

General information: Dispose in accordance with all applicable regulations.

Disposal methods: Do not empty into drains; dispose of this material and its container in a safe way. When storing used products, ensure that the waste categories and mixing instructions are observed.

List of Waste (LoW) Codes

12 03 01*: aqueous washing liquids

SECTION 14: Transport information

ADR/RID

14.1 UN number or ID number: —
 14.2 UN Proper Shipping Name: —
 14.3 Transport Hazard Class(es)
 Class: Non-dangerous goods
 Label(s): —
 Hazard No. (ADR): —
 Tunnel restriction code: —
 14.4 Packing Group: —
 14.5 Environmental hazards: —
 14.6 Special precautions for user: —

IMDG

14.1 UN number or ID number: —
 14.2 UN Proper Shipping Name: —
 14.3 Transport Hazard Class(es)
 Class: Non-dangerous goods
 Label(s): —
 EmS No.: —
 14.3 Packing Group: —
 14.5 Environmental hazards: —
 14.6 Special precautions for user: —

Product name: MAINTAIN SCREENWASH

IATA

- 14.1 UN number or ID number: –
14.2 Proper Shipping Name: –
14.3 Transport Hazard Class(es):
 Class: Non-dangerous goods
 Label(s): –
14.4 Packing Group: –
14.5 Environmental hazards: –
14.6 Special precautions for user: –

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code: Not applicable.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:

GB Regulations

The Ozone-Depleting Substances and Fluorinated Greenhouse Gases (Amendment etc.) (EU Exit) Regulations 2019:
none

The Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020:
none

15.2 Chemical safety assessment: No Chemical Safety Assessment has been carried out.

DIRECTIVE Control of Major Accident Hazards Regulations 2015:

Hazard category in accordance with GB-CLP	Qualifying quantity for the application of Lower-tier requirements:	Qualifying quantity for the application of Upper-tier requirements:
P5c: P5c. Flammable liquids	5.000 t	50.000 t
P5a: P5a. Flammable liquids	10 t	50 t
P5b: P5b. Flammable liquids	50 t	200 t

SECTION 16: Other information

Revision Information: Vertical lines in the margin indicate an amendment.

Wording of the H-statements in section 2 and 3

- H225 Highly flammable liquid and vapor.
H226 Flammable liquid and vapor.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Other information: The classification complies with the current GB lists; however, it has been supplemented with expert literature information and information provided

Product name: MAINTAIN SCREENWASH

by/about our company. The following evaluation methods were used: On the basis of test data; Calculation Method; Bridging Principle "Substantially similar mixtures"; Expert Judgement

Revision Date:

23.02.2023

Disclaimer:

The data contained in this safety data sheet are based on our current knowledge and experience and are given to the best of our knowledge and belief. It characterizes the product only with regard to safety requirements for handling, transport and disposal. The data do not describe the product's properties (tech. product specification). Neither should any agreed property nor the suitability of the product for any specific technical application be deduced from the data contained in this safety data sheet. Modifications on this document are not allowed. The data are not transferable to other products. In the case of mixing the product with other products or in the case of processing, the data in this safety data sheet are not necessarily valid for the new-made material. It is the responsibility of the recipient of the product to observe federal, state and local law. Please contact us to obtain up-to-date safety data sheets. This document was issued electronically and has no signature.