


Spherical roller bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_U	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			C	C_0	kN	r/min		kg	* - SKF Explorer bearing
85	150	36	285	325	34,5	4000	5600	2,60	22217 EK *



Calculation factors

e 0,22
 Y_1 3
 Y_2 4,6
 Y_0 2,8