




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Insulation Resistance	1000 MΩ
Operating Voltage	300 VAC

Body Features

Primary Product Color	Yellow
-----------------------	--------



Contact Features

Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Type	Tab
Contact Retention Within Housing	Without
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Height	8.9 mm[.35 in]
Connector Length	29 mm[1.14 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Melamine (3% in 23796019081) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 176272-6
AMP UNIVERSAL POWER PLUG 3P



TE Part # 176272-1
AMP UNIVERSAL POWER PLUG 3P




TE Part # 175153-1
UNIV POWER TAB CONT L/P




TE Part # 175154-1
UNIV POWER TAB CONT L/P






TE Part # 176272-2
AMP UNIVERSAL POWER PLUG 3P



TE Part # 175153-2
U/P TAB CONT L/P



TE Part # 176272-4
AMP UNIVERSAL POWER PLUG 3P




TE Part # 175149-3
AMP UNIVERSAL POWER CONN.TAB
C




TE Part # 175154-2
U/P TAB CONT L/P



TE Part # 176272-9
AMP UNIVERSAL POWER PLUG 3P



TE Part # 175149-2
AMP UNIVE. POWER CONN TAB
CONT



TE Part # 175149-1
UNIVERSAL POWER CONN TAB



TE Part # 175150-1
UNIVERSAL POWER CONN TAB



TE Part # 175150-2
AMP UNIVE. POWER CONN TAB
CONT


Also in the Series | AMP Universal Power



Connector Contacts(22)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(51)



Power Contacts(21)



Rectangular Connector Housings(112)



Rectangular Power Connectors(163)



Wire-to-Board Headers & Receptacles
(51)

Customers Also Bought




TE Part #926894-1
UNIV.M-N-L.PIN




TE Part #350782-1
09P UMNL CAP HSG



TE Part #1011-259-0305
BKSHL, 3P, BLK, PLG,ST,SR,NW6/7.5/8.5/10



TE Part #CAT-J96-ULPA
Unsealed Locks and Position Assurance 5/10



TE Part #2-1747066-2
GRACE INERTIA CONN 2.5 PLUG HSG 2P BLUE



TE Part #794278-1
09P UMNL WIRE SEAL



TE Part #1670865-1
COVER,90



TE Part #2174308-1
POSITIVE LOCK EX .250 (6.3 MM)



TE Part #234156-9
CRIMPER,WIRE SPECIAL

Documents

Product Drawings

UNIV POWER CAP HSG 3P P/MOUNT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_176293-4_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_176293-4_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_176293-4_G.3d_stp.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_176293-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_176293-4_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_176293-4_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Crimping of Universal Power Contact](#)

English

[Product Specification](#)

Japanese

[AMP Universal Power Connector](#)

Japanese

Instruction Sheets

[AMP UNIVERSAL POWER CONNECTOR SERIES](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English