




Connectors > Rectangular Connectors > Standard Rectangular Connectors > DYNAMIC 4000 REC AND TAB HSG



Connector Product Type: **Housing**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **6.35 mm [.25 in]**

Number of Rows: **1**

[All DYNAMIC 4000 REC AND TAB HSG \(27\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
--------------------	-----------------

Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1747276-2
DYNAMIC D4200 REC HSG 2P/X



TE Part # 2822901-1
ADAPTER,DIN RAIL ATTACHMENT
D4200S

Also in the Series | Dynamic 4000 Series



Connector Contacts(17)	Connector Hardware(2)	Power Contacts(17)	Rectangular Connector Housings(27)
Rectangular Power Connectors(48)	Standard Rectangular Connectors(27)	Wire-to-Board Connector Assemblies & Housings(2)	

Customers Also Bought

TE Part #350866-1 01P UMNL CAP HSG	TE Part #1747499-2 DYNAMIC D4200 REC CONT M/LP	TE Part #2-179552-3 DYNAMIC D-3200 WTW TAB HSG 3P	TE Part #T2111028101-000 HMN-D2-MC
TE Part #9-1827862-5 DYNAMIC 1100D REC HSG 10P X BLACK	TE Part #CAT-D9934-A15C DYNAMIC 1500T REC AND TAB HSG	TE Part #CAT-D9934-A15B Receptacle and Tab Housing: 2.5 mm Pitch, 250V	TE Part #674983J001 V2-7.0-0-SP-SM

Documents

Product Drawings
DYNAMIC 4200S TAB HSG 2P F/H X
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-1747414-2_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-1747414-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1747414-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[TUV Certificate](#)

English