

Features

- Flexible polyurethane (PUR) spiral power cable
- 3-core H05BQ-F construction with 0.75 mm² conductors
- 2 m extended length with space-saving coiled design
- Tinned copper conductors for enhanced durability
- Black semi-gloss PUR outer sheath with EPR/EPDM insulation
- Operating temperature range: -25°C to +70°C

RS PRO Spiral Cable TB28 FLEX BQ-F power cable 3G0,75mm², 0.5m / 2.0m Polyurethane (PUR)

RS Stock No.: 283-6004



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Spiral Cable H05BQ-F TB28 FLEX power cable is a high-quality spiral cable designed to provide a reliable and durable power connection in applications requiring flexibility and repeated movement. Constructed with 3-core tinned copper conductors, the cable offers dependable electrical performance and enhanced resistance to corrosion. A robust black polyurethane (PUR) outer sheath provides good resistance to abrasion, mechanical wear, and frequent flexing, helping to extend service life in demanding environments. The coiled design allows the cable to extend when required and retract when not in use, supporting efficient cable management and reducing clutter.

This cable is commonly used for connecting movable equipment, machinery, automation systems, and portable electrical devices where flexibility and durability are important. Typical applications include industrial machinery, material handling equipment, workstations, production equipment, and power supply connections subject to regular movement. Suitable for operation in temperatures ranging from -25°C to +70°C, the cable is designed for use in industrial and commercial environments where reliable power transmission and mechanical protection are required.

General Specifications

Brand	RS PRO
Product Type	Spiral Cable
Series	TB28 FLEX BQ-F power cable
Number of cores	3
Cable CSA	0,75 mm ²
Shielding	No
Jacket Material	Polyurethane (PUR)
Jacket colour	Black (semi-glossy)
Conductor type	42x0,15 mm Tinned copper
Conductor insulation	EPR/EPDM
Conductor colours	Blue, Brown + Yellow/Green

Mechanical Specifications

Cable diameter	7,40mm
Conductor diameter	2,40mm
Spiral diameter	25,80mm
Retracted spiral cable length	0.5m
Extended spiral cable length	2m
Weight	0.28kg
Extension rate	4

Operation Environment Specifications

Minimum operating temperature	-25 °C
Maximum operating temperature	70 °C


Approvals

Compliance/Certifications	RoHS; EN 50525-2-21
---------------------------	---------------------

Dimensional Drawing

*Dimensions below in mm

Key to Standard Diagram	
L	2000
L0	500
ØD	7,4
ØD0	25,8
L1	200
L2	200
L3	
L4	
L5	
L6	



Tolerances ± 10% unless stated otherwise