

Eaton 265318

Catalog Number: 265318

Eaton Distribution parts. Impulse relay, 8AC, 2W, 16A, 50Hz, 2SU

General specifications



Product Name

Eaton Distribution parts

EAN

4015082653187

Product Height

70 mm

Product Weight

0.263 kg

Catalog Number

265318

Product Length/Depth

80 mm

Product Width

35 mm

Compliances

RoHS conform

Product specifications

Mounting method

DIN rail

Control voltage 1 type

AC

Ambient operating temperature - max

45 °C

Ambient operating temperature - min

-20 °C

Control voltage 1 - max

8 V

Control voltage 1 - min

8 V

Control voltage 2 - max

0 V

Control voltage 2 - min

0 V

Frequency control voltage 1 - max

50 Hz

Frequency control voltage 1 - min

50 Hz

Frequency control voltage 2 - max

0 Hz

Frequency control voltage 2 - min

0 Hz

Heat dissipation per pole, current-dependent

1.5 W

Incandescent lamp load - max

0 W

Load fluorescent lamp - max

0 VA

Load fluorescent lamp (duo circuit) - max

0 VA

Load fluorescent lamp (parallel compensated) - max

0 VA

Number of contacts (change-over contacts)

Resources

Declarations of conformity

[DA-DC-03_Z-S](#)

[DA-DC-03_Z-S_SC_SB](#)

Drawings

[eaton-wiring-diagram-z-s-2te.jpg](#)

[eaton-dimensions-mas-z-s230.jpg](#)

[eaton-3d-drawing-z-s230-scha2.jpg](#)

2

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Rated operational current for specified heat dissipation (In)

16 A

Rated switch current

16 A

Equipment heat dissipation, current-dependent

3 W

Supply voltage - max

415 V

Supply voltage - min

240 V

Switching current (cos phi = 0.6) - max

0 A

Width in number of modular spacings

2

Built-in depth

60 mm

Operating mode

Manual operation possible

Control voltage 2 type

AC

Voltage type

AC

Functions

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia