

CAT. N° 0 277 72



## CAM SWITCH - 3-PHASE MOTOR SWITCH STARTER 1 WAY, 2 SPEED O-PV-GV - PR 12 - BOX

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,981
Weight (g)	409,00

### Product characteristics

#### Function: 3-phase motor switch

#### Starter 1 way, 2 speed Dalhandler

- Range : PR 12
- Max. rating AC 3 : 4 kW
- Number of contacts : 8

### General characteristics

#### Cam switches insulating box

- For selecting and changing the status of the circuits into which it is integrated
- For viewing the state of equipment according to the position of the selector lever
- Boxed device, class II
- Contacts with positive opening and double breaking of poles
- Presentation: black or grey/black selector lever, faceplate with marking
- Conform to standards IEC EN 60947-3
- IP 65 for 76 x 76 and 96 x 120 mm boxes
- IP 55 for 135 x 170 mm boxes

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.356\)](#)
- [Technical page \(p.357\)](#)
- [Technical page \(p.358-359\)](#)



#### Agreements & certificates of conformity

- [CSA-1725160](#)
- [QC / CB-FR 60026094B](#)
- [UL recogn-280206-E57817](#)



#### Installation instructions & related documents

- [096897001-01](#)