

## A52.080/1, -30...+50°C, 160x8mm

### Bimetal Thermometer, Industrial Series

Item number: 3903842

Quantity: 1 pcs.

Order code: A52.080-1-CCB-BS-C160GZZ-Z-ZZZ TD FZZVC-  
AZ1ZZZZZZZZZZ

Overview: A52.080/1, -30...+50°C, 160x8mm  
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)  
flat instrument glass  
\*WIKA\*

Details: Bimetal Thermometer, Industrial Series  
Specifications according to data sheet: TM 52.01  
Accuracy class: class 1 per EN 13190  
Case: stainless steel  
Stem material: stainless steel  
Model: A52.080, nominal size 80, location of stem centre back  
Connection design: 1, plain stem  
Scale range: -30 °C ... +50 °C  
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)  
Stem diameter: 8 mm  
Insertion length L1: 160 mm  
norm-mark on dial: \*EN 13190\*  
accuracy class on dial: \*Cl.1\*  
Bimetallic thermometer, for industrial applications A52L  
Specifications according to data sheet: TM 52.01  
Accuracy class: class 1 per EN 13190  
Case: stainless steel  
Stem material: stainless steel  
Model: A52.080, nominal size 80, location of stem centre back  
Connection design: 1, plain stem  
Scale range: -30 °C ... +50 °C  
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)  
Stem diameter: 8 mm  
Insertion length L1: 160 mm  
Window: flat instrument glass  
Case: Stainless steel  
Ingress protection: IP 43  
Manufacturer logo: \*WIKA\*  
Stem material: stainless steel