

## TINNED ALUMINUM EARTHING AND NEUTRAL DOUBLE BUSBAR



Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications such as switchgear and control equipment, electrical equipment, for wind and solar power generation and data centers.

### CERTIFICATIONS



### FEATURES

Tinned aluminum bar allows for copper or aluminum conductor connections

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Tin plating is corrosion resistant

Rigid bar

Can be fixed using IRS Angle Support Bracket, DMH Metallic Spacer or DH Distance Holder and Spacer

Quick and easy installation

RoHS compliant

### SPECIFICATIONS


**Material:** Aluminum

**Finish:** Tinned

Catalog Number	EBD8AL	EBD10AL	EBD14AL	EBD20AL	EBD26AL	EBD34AL	EBD44AL
Article Number	568716	568717	568718	568719	568720	568721	568722

Catalog Number	EBD8AL	EBD10AL	EBD14AL	EBD20AL	EBD26AL	EBD34AL	EBD44AL
Number of Connections	8	10	14	20	26	34	44
Conductor Size, IEC	(1) 16 - 35 mm <sup>2</sup> Stranded (4) 6 - 10 mm <sup>2</sup> Stranded (3) 1.5 - 6 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (5) 6 - 10 mm <sup>2</sup> Stranded (4) 1.5 - 6 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (7) 6 - 10 mm <sup>2</sup> Stranded (6) 1.5 - 6 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (1) 16 - 50 mm <sup>2</sup> Stranded (9) 1.5 - 6 mm <sup>2</sup> Stranded (9) 6 - 10 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (1) 16 - 50 mm <sup>2</sup> Stranded (12) 1.5 - 6 mm <sup>2</sup> Stranded (12) 6 - 10 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (1) 16 - 50 mm <sup>2</sup> Stranded (16) 1.5 - 6 mm <sup>2</sup> Stranded (16) 6 - 10 mm <sup>2</sup> Stranded	(1) 16 - 35 mm <sup>2</sup> Stranded (1) 16 - 50 mm <sup>2</sup> Stranded (21) 1.5 - 6 mm <sup>2</sup> Stranded (21) 6 - 10 mm <sup>2</sup> Stranded
Conductor Size, UL	(1) #4 - #2 Stranded (3) #16 - #10 Stranded (4) #8 - #6 Stranded	(1) #4 - #2 Stranded (4) #16 - #10 Stranded (5) #8 - #6 Stranded	(1) #4 - #2 Stranded (6) #16 - #10 Stranded (7) #8 - #6 Stranded	(1) #1 - #1/0 Stranded (1) #4 - #2 Stranded (9) #16 - #10 Stranded (9) #8 - #6 Stranded	(1) #1 - #1/0 Stranded (1) #4 - #2 Stranded (12) #8 - #6 Stranded (12) #16 - #10 Stranded	(1) #1 - #1/0 Stranded (1) #4 - #2 Stranded (16) #8 - #6 Stranded (16) #16 - #10 Stranded	(1) #1 - #1/0 Stranded (1) #4 - #2 Stranded (21) #16 - #10 Stranded (21) #8 - #6 Stranded
Max Current Rating	115A	115A	115A	115A	150A	150A	150A
Height (H)	1/2"	1/2"	1/2"	1/2"	1/2"	1/2"	1/2"
Width (W)	2 1/2"	3"	3.53"	4.86"	5.88"	7.39"	9.04"
Depth (D)	0.5"	0.5"	0.5"	0.5"	0.5"	0.5"	0.5"
Unit Weight	0.07 lb	0.09 lb	0.11 lb	0.15 lb	0.18 lb	0.22 lb	0.27 lb
Certification Details		UL® 486A UL® 486B	UL® 486A UL® 486B	UL® 486A UL® 486B	UL® 486A UL® 486B	UL® 486A UL® 486B	UL® 486A UL® 486B

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**