

The lightest gloves combining cut-resistance, oil-repellence and up to 12x the durability**

- RIPEL technology prevents oil from making contact with the skin, keeping hands safe and dry
- Ansell GRIP technology delivers an average of 13% better grip performance for safer handling of wet or oily materials*
- FORTIX technology provides extended use life
 - up to 12x the durability in the thumb crotch region for superior protection
 - up to 40% improved abrasion resistance*
- Lightest weight: up to 20% lighter design and ZONZ comfort fit technology delivering all day comfort*

Palm coated



3/4 dipped



Fully coated



Industries

- Automotive
- Machinery & Equipment
- Metal Fabrication

Applications

- Body Shop
- Component Assembly
- Final Assembly
- Machining
- Maintenance
- Material Handling
- Milling
- Stamping & Press
- Primary Assembly

* vs competitive set

** vs unreinforced glove equivalent

Performance Profile

- Provides protection from cuts and oil exposure across multiple applications and within a series of different dip-line gloves (palm coated, 3/4 dipped, full dipped)
- RIPEL technology prevents fluid from making contact with the workers skin, keeping hands dry.
- Provides dexterity and a high level of comfort with ZONZ technology.
- Superior grip performance with ANSELL GRIP technology for safe handling in dry-to-oily applications.
- FORTIX technology for extended product use life and increased protection with up to 12x durability in the thumb crotch.

Key Features

- Protects against lacerations, oil and industrial fluid exposure.
- Ultra-lightweight 18 gauge

design provides dexterity and a high level of comfort.

- Reinforced thumb crotch for increased protection & longevity.
- Grip performance for safe handling in dry-to-oily applications.
- High durability FORTIX coating for extended product use life.
- Silicone free.

Technologies



RIPEL™
Liquid Repellence Technology

ANSELL GRIP™
Ansell Grip Technology

ZONZ™
Comfort Fit Technology

FORTIX™
Abrasion Resistance Technology

Performance Standards



HyFlex 11-931



HyFlex 11-937



HyFlex 11-939

Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
HyFlex 11-931	11-931: Palm Coated	18	6-11	212-261 mm	Black liner with black and grey coating	144 pairs/case
HyFlex 11-937	11-937: 3/4 Coated					
HyFlex 11-939	11-939: Fully Coated					
	Coating Material: Nitrile/PU Blend Liner Material: HPPE Dyneema Diamond Cuff Style: Knitwrist					

Europe, Middle East & Africa

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
+32 2 528 74 00
+32 2 528 74 01

Russia

Анселл РУС
123610 Россия, Москва
Краснопресненская
Наб. 12, п.3, оф. 1103
Тел. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates, except as noted. Dyneema® is a trademark of DSM. Use of this trademark is prohibited unless strictly authorized. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarketing © 2016 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.