


DX2041



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC



panel cutout 91 x 43 mm



Product characteristics	
Housing	housing for panel mounting
Dimensions [mm]	48 x 112 x 116
Application	
Application	displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors
Electrical data	
Frequency AC [Hz]	50...60
Operating voltage [V]	115...230 AC / 18...30 DC
Current consumption [mA]	100
Inputs / outputs	
Number of inputs and outputs	Number of analogue inputs: 2
Inputs	
Number of analogue inputs	2; (Spannungs- oder Stromeingang)
Analogue input (current) [mA]	0...20
Analogue input (voltage) [V]	-10...10
Resolution of analogue input	16 bit
Precision analogue input [%]	0,1
Operating conditions	
Ambient temperature [°C]	-20...60
Storage temperature [°C]	-25...70
Protection	IP 65
Protection rating terminals	IP 20
Tests / approvals	
EMC	EN 61000-6-2
	EN 61000-6-3
	EN 61000-6-4

DX2041



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC


Mechanical data	
Weight [g]	351
Housing	housing for panel mounting
Type of mounting	installation in panels or panel cutouts; (panel cutout: 91 x 43 mm)
Dimensions [mm]	48 x 112 x 116
Materials	Noryl UL94-V-0

Displays / operating elements	
Display	colour display full graphic LCD display, touch screen

Electrical connection

screw terminals:

Connection



NC not used