

**40V COMPLEMENTARY PAIR ENHANCEMENT MODE MOSFET**

**Product Summary**

Device	V <sub>(BR)DSS</sub>	R <sub>DS(on)</sub> max	I <sub>D</sub> max T <sub>A</sub> = 25°C (Notes 3 & 5)
Q1	40V	45mΩ @ V <sub>GS</sub> = 10V	5.5A
		60mΩ @ V <sub>GS</sub> = 4.5V	4.2A
Q2	-40V	45mΩ @ V <sub>GS</sub> = -10V	-5.8A
		60mΩ @ V <sub>GS</sub> = -4.5V	-4.2A

**Description and Applications**

This MOSFET has been designed to ensure that R<sub>DS(on)</sub> of N and P channel FET are matched to minimize losses in both arms of the bridge. The DMC4040SSD is optimized for use in 3 phases brushless DC motor circuits (BLDC), CCFL backlighting.


- 3 phases BLDC motor
- CCFL backlighting

**Features and Benefits**


- Matched N & P R<sub>DS(on)</sub> - Minimizes power losses
- Fast switching – Minimizes switching losses
- Dual device – Reduces PCB area
- "Green" component and RoHS compliant (Note 1)
- Qualified to AEC-Q101 Standards for High Reliability

**Mechanical Data**



- Case: SO-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0 (Note 1)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - Matte Tin annealed over Copper lead frame. Solderable per MIL-STD-202, Method 208
- Weight: 0.074 grams (approximate)



Top View



Top View




Equivalent Circuit

**Ordering Information** (Note 1)

Product	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DMC4050SSD-13	C4050SD	13	12	2,500

Notes: 1. Diodes, Inc. defines "Green" products as those which are RoHS compliant and contain no halogens or antimony compounds; further information about Diodes Inc.'s "Green" Policy can be found on our website. For packaging details, go to our website.

**Marking Information**



Ⓜ = Manufacturer's Marking  
 C4050SD = Product Type Marking Code  
 YYWW = Date Code Marking  
 YY = Year (ex: 10 = 2010)  
 WW = Week (01 - 53)

**Maximum Ratings** @ $T_A = 25^\circ\text{C}$  unless otherwise specified


Characteristic			Symbol	N-Channel - Q1	P-Channel - Q2	Units
Drain-Source Voltage			$V_{DSS}$	40	-40	V
Gate-Source Voltage			$V_{GSS}$	$\pm 20$	$\pm 20$	
Continuous Drain Current	$V_{GS} = 10\text{V}$	(Notes 3 & 5)	$I_D$	5.8	-5.8	A
		$T_A = 70^\circ\text{C}$ (Notes 3 & 5)		4.38	-4.52	
		(Notes 2 & 5)		4.2	-4.2	
		(Notes 2 & 6)		5.3	-5.3	
Pulsed Drain Current	$V_{GS} = 10\text{V}$	(Notes 4 & 5)	$I_{DM}$	24.1	-24.9	
Continuous Source Current (Body diode)			$I_S$	2.5	-2.5	
Pulsed Source Current (Body diode)			$I_{SM}$	24.1	-24.9	

**Thermal Characteristics** @ $T_A = 25^\circ\text{C}$  unless otherwise specified


Characteristic		Symbol	N-Channel - Q1	P-Channel - Q2	Unit
Power Dissipation Linear Derating Factor	(Notes 2 & 5)	$P_D$	1.25		W mW/ $^\circ\text{C}$
			10		
	(Notes 2 & 6)		1.8		
	(Notes 3 & 5)		14.3		
Thermal Resistance, Junction to Ambient	(Notes 2 & 5)	$R_{\theta JA}$	2.14		$^\circ\text{C}/\text{W}$
	(Notes 2 & 6)		17.2		
	(Notes 3 & 5)		100		
			70		
Thermal Resistance, Junction to Lead	(Notes 3 & 5)	$R_{\theta JL}$	58		
Operating and Storage Temperature Range			$T_J, T_{STG}$	-55 to +150	$^\circ\text{C}$

- Notes:
2. For a device surface mounted on 25mm x 25mm x 1.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions; the device is measured when operating in a steady-state condition.
  3. Same as note (2), except the device is measured at  $t \leq 10$  sec.
  4. Same as note (2), except the device is pulsed with  $D = 0.02$  and pulse width 300 $\mu\text{s}$ .
  5. For a dual device with one active die.
  6. For a device with two active die running at equal power.
  7. Thermal resistance from junction to solder-point (at the end of the drain lead).


**Thermal Characteristics**




**N-channel Safe Operating Area**




**P-channel Safe Operating Area**



**Transient Thermal Impedance**



**Derating Curve**



**Pulse Power Dissipation**

**Electrical Characteristics N-CHANNEL** @ $T_A = 25^\circ\text{C}$  unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS (Note 8)</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	40	-	-	V	$V_{GS} = 0V, I_D = 250\mu A$
Zero Gate Voltage Drain Current $T_J = 25^\circ\text{C}$	$I_{DSS}$	-	-	1.0	$\mu A$	$V_{DS} = 40V, V_{GS} = 0V$
Gate-Source Leakage	$I_{GSS}$	-	-	$\pm 100$	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
<b>ON CHARACTERISTICS (Note 8)</b>						
Gate Threshold Voltage	$V_{GS(th)}$	0.8	1.3	1.8	V	$V_{DS} = V_{GS}, I_D = 250\mu A$
Static Drain-Source On-Resistance	$R_{DS(ON)}$	-	20	45	m $\Omega$	$V_{GS} = 10V, I_D = 3A$
		-	33	60		$V_{GS} = 4.5V, I_D = 3A$
Forward Transfer Admittance	$ Y_{fs} $	-	12.6	-	S	$V_{DS} = 5V, I_D = 3A$
Diode Forward Voltage (Note 8)	$V_{SD}$	-	0.7	1.0	V	$V_{GS} = 0V, I_S = 1A$
<b>DYNAMIC CHARACTERISTICS (Note 9)</b>						
Input Capacitance	$C_{iss}$	-	1790.8	-	pF	$V_{DS} = 20V, V_{GS} = 0V,$ $f = 1.0\text{MHz}$
Output Capacitance	$C_{oss}$	-	160.6	-	pF	
Reverse Transfer Capacitance	$C_{rss}$	-	120.5	-	pF	
Gate Resistance	$R_g$	-	1.03	-	$\Omega$	$V_{DS} = 0V, V_{GS} = 0V, f = 1\text{MHz}$
Total Gate Charge	$Q_g$	-	37.56	-	nC	$V_{GS} = 10V, V_{DS} = 20V,$ $I_D = 3A$
Gate-Source Charge	$Q_{gs}$	-	7.8	-	nC	
Gate-Drain Charge	$Q_{gd}$	-	6.6	-	nC	
Turn-On Delay Time	$t_{D(on)}$	-	8.08	-	ns	$V_{GS} = 10V, V_{DS} = 20V,$ $I_D = 3A$
Turn-On Rise Time	$t_r$	-	15.14	-	ns	
Turn-Off Delay Time	$t_{D(off)}$	-	24.29	-	ns	
Turn-Off Fall Time	$t_f$	-	5.27	-	ns	

Notes: 8. Short duration pulse test used to minimize self-heating effect.  
9. Guaranteed by design. Not subject to production testing.




Fig. 1 Typical Output Characteristic




Fig. 2 Typical Transfer Characteristic

**DMC4050SSD**




Fig. 3 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 4 Typical On-Resistance vs. Drain Current and Temperature




Fig. 5 On-Resistance Variation with Temperature




Fig. 6 On-Resistance Variation with Temperature




Fig. 7 Gate Threshold Variation vs. Ambient Temperature




Fig. 8 Diode Forward Voltage vs. Current

**DMC4050SSD**




Fig. 9 Typical Total Capacitance




Fig. 10 Typical Leakage Current vs. Drain-Source Voltage




Fig. 11 Gate-Charge Characteristics




Fig. 12 Transient Thermal Response

**Electrical Characteristics P-CHANNEL** @ $T_A = 25^\circ\text{C}$  unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS (Note 8)</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	-40	-	-	V	$V_{GS} = 0V, I_D = -250\mu A$
Zero Gate Voltage Drain Current $T_J = 25^\circ\text{C}$	$I_{DSS}$	-	-	-1.0	$\mu A$	$V_{DS} = -40V, V_{GS} = 0V$
Gate-Source Leakage	$I_{GSS}$	-	-	$\pm 100$	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
<b>ON CHARACTERISTICS (Note 8)</b>						
Gate Threshold Voltage	$V_{GS(th)}$	-0.8	-1.3	-1.8	V	$V_{DS} = V_{GS}, I_D = -250\mu A$
Static Drain-Source On-Resistance	$R_{DS(on)}$	-	28 30	45 60	$m\Omega$	$V_{GS} = -10V, I_D = -3A$ $V_{GS} = -4.5V, I_D = -3A$
Forward Transfer Admittance	$ Y_{fs} $	-	16.6	-	S	$V_{DS} = -5V, I_D = -3A$
Diode Forward Voltage (Note 8)	$V_{SD}$	-	-0.7	-1.0	V	$V_{GS} = 0V, I_S = -1A$
<b>DYNAMIC CHARACTERISTICS (Note 9)</b>						
Input Capacitance	$C_{iss}$	-	1643.17	-	pF	$V_{DS} = -20V, V_{GS} = 0V,$ $f = 1.0\text{MHz}$
Output Capacitance	$C_{oss}$	-	179.13	-	pF	
Reverse Transfer Capacitance	$C_{rss}$	-	127.82	-	pF	
Gate Resistance	$R_g$	-	6.43	-	$\Omega$	$V_{DS} = 0V, V_{GS} = 0V, f = 1\text{MHz}$
Total Gate Charge	$Q_g$	-	33.66	-	nC	$V_{GS} = -10V, V_{DS} = -20V,$ $I_D = -3A$
Gate-Source Charge	$Q_{gs}$	-	5.54	-	nC	
Gate-Drain Charge	$Q_{gd}$	-	7.30	-	nC	
Turn-On Delay Time	$t_{D(on)}$	-	6.85	-	ns	$V_{GS} = -10V, V_{DS} = -20V,$ $I_D = -3A$
Turn-On Rise Time	$t_r$	-	14.72	-	ns	
Turn-Off Delay Time	$t_{D(off)}$	-	53.65	-	ns	
Turn-Off Fall Time	$t_f$	-	30.86	-	ns	

Notes: 8. Short duration pulse test used to minimize self-heating effect.  
9. Guaranteed by design. Not subject to production testing.




Fig. 13 Typical Output Characteristic




Fig. 14 Typical Transfer Characteristic

**DMC4050SSD**




Fig. 15 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 16 Typical On-Resistance vs. Drain Current and Temperature




Fig. 17 On-Resistance Variation with Temperature




Fig. 18 On-Resistance Variation with Temperature




Fig. 19 Gate Threshold Variation vs. Ambient Temperature




Fig. 20 Diode Forward Voltage vs. Current



**DMC4050SSD**




Fig. 21 Typical Total Capacitance




Fig. 22 Typical Leakage Current vs. Drain-Source Voltage




Fig. 23 Gate-Charge Characteristics






Fig. 24 Transient Thermal Response

**Package Outline Dimensions**



SO-8		
Dim	Min	Max
A	-	1.75
A1	0.10	0.20
A2	1.30	1.50
A3	0.15	0.25
b	0.3	0.5
D	4.85	4.95
E	5.90	6.10
E1	3.85	3.95
e	1.27 Typ	
h	-	0.35
L	0.62	0.82
θ	0°	8°
All Dimensions in mm		

**Suggested Pad Layout**



Dimensions	Value (in mm)
X	0.60
Y	1.55
C1	5.4
C2	1.27

#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2011, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)