


Geberit Mapress Stainless Steel bend with plain end



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5

- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	arc °	L cm	H cm	Z cm
36111	12	15	15	3	4	1
36113	20	22	15	3.2	4.1	1.1
36114	25	28	15	3.6	4.3	1.3
36115	32	35	15	3.2	4.1	0.6

Art. no.	DN	d _g mm	arc °	L cm	H cm	Z cm
36116	40	42	15	3.7	4.7	0.7
36117	50	54	15	4.4	5.5	0.9
36118	65	76.1	15	7.5	8.4	2.2
36119	80	88.9	15	8.5	9.5	2.5
36120	100	108	15	10.3	11.7	2.8
36131	12	15	30	3.3	4.3	1.3
36133	20	22	30	3.7	4.6	1.6
36134	25	28	30	4.1	4.8	1.8
36135	32	35	30	3.7	4.6	1.1
36136	40	42	30	4.4	5.4	1.4
36137	50	54	30	5.2	6.3	1.7
36138	65	76.1	30	8.8	9.7	3.5
36139	80	88.9	30	10.1	11.1	4.1

Art. no.	DN	d _g mm	arc °	L cm	H cm	Z cm
36140	100	108	30	12.2	13.6	4.7
30702	12	15	45	2.8	3.6	0.8
30703	15	18	45	2.9	3.6	0.9
30704	20	22	45	3.2	4	1.1
30705	25	28	45	3.7	4.4	1.4
32706	32	35	45	4.3	5	1.7
32707	40	42	45	5.1	5.9	2.1
32708	50	54	45	6.2	7	2.7
32709	65	76.1	45	10.3	11.1	5
32710	80	88.9	45	11.7	12.8	5.7
32711	100	108	45	14.3	15.8	6.8
36171	12	15	60	4	5	2
36173	20	22	60	4.7	5.6	2.6

Art. no.	DN	d _ø mm	arc °	L cm	H cm	Z cm
36174	25	28	60	5.4	6.1	3.1
36175	32	35	60	5	5.9	2.4
36176	40	42	60	5.9	6.9	2.9
36177	50	54	60	7.2	8.3	3.7
36178	65	76.1	60	11.7	12.6	6.4
36179	80	88.9	60	13.6	14.6	7.6
36180	100	108	60	16.6	18	9.1
30302	12	15	90	3.8	4.8	1.8
30303	15	18	90	4.2	5.1	2.2
30304	20	22	90	4.7	5.8	2.6
30305	25	28	90	5.7	6.3	3.4
33306	32	35	90	6.8	7.4	4.2
33307	40	42	90	8	8.8	5

Art. no.	DN	d _ø mm	arc °	L cm	H cm	Z cm
33308	50	54	90	10	10.8	6.5
33309	65	76.1	90	15.7	16.7	10.4
33310	80	88.9	90	18.4	19.5	12.4
33311	100	108	90	22.6	24.1	15.1