

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product

Produit

Linear Power Supplies

Name and address of the applicant

Nom et adresse du demandeur

Power-One, Inc

740 Calle Plano, Camarillo, CA 93012-8583

Name and address of the manufacturer

Nom et adresse du fabricant

24238, 24258, 24260, 36080

Name and address of the factory

Nom et adresse de l'usine

See Manufacturer

Rating and principal characteristics

Valeurs nominales et caractéristiques principales

Rated Voltage: 100/120/220/230/240 V AC

Rated Frequency: 50 / 60 Hz

Rated Input Current: See Attachment

Rated Output Voltage: See Attachment

Rated Output Current: See Attachment

Trade mark (if any)

Marque de fabrique (si elle existe)

Power-One

Model/type Ref.

Ref. de type

CP323

(see attachment for additional models)

Additional information (if necessary)

Information complémentaire (si nécessaire)

Protection Class I (at end-use)

A sample of the product was tested and
found to be in conformity with

*Un échantillon de ce produit a été essayé et a été
considéré conforme à la*

PUBLICATION
IEC 60950:1999

EDITION
Third

as shown in the Test Report Ref. No.
which form part of this certificate
*comme indiqué dans le Rapport d'essais numéro de
référence*

qui constitue une partie de ce certificat

TÜV Product Service
095-SI100277-127

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

Department: ELS SDG /C. Ortiz

Date: 17-07-01

CB 01 07 24238 231



TÜV
PRODUCT SERVICE

TÜV PRODUCT SERVICE GMBH · Certification Body · Ridlerstrasse 65 · D-80339 München

Appendix to CB Certificate Ref. No: DE 3 - 5955

Ratings:

Model:	Required input fuse	Input (AC)			Output #1:		Output #2:		Required airflow (linear feet per minute)
	A	Vac	A	Hz	Vdc	A	Vdc	A	lfm
HN5-9/OVP	2.0	100/120	2.0	50/60	5	9.0	—	—	70
	1.0	220/230/240	1.0						
HN12-5.1	2.0	100/120	2.0	50/60	12	5.1	—	—	120
	1.0	220/230/240	1.0						
HN15-4.5	2.0	100/120	2.0	50/60	15	4.5	—	—	100
	1.0	220/230/240	1.0						
HN24-3.6	2.0	100/120	2.0	50/60	24	3.6	—	—	120
	1.0	220/230/240	1.0						
HN28-3	2.0	100/120	2.0	50/60	28	3.0	—	—	100
	1.0	220/230/240	1.0						
CP323	2.0	100/120	2.0	50/60	5	2.0	12	4.0	100
	1.0	220/230/240	1.0						

The model name may be followed by suffix -A. Suffix after the first hyphen may be replaced by -5XX or -7XX where X is 0-9.

Date: 01-07-17

Signature:

