


ELH, Aluminum Electrolytic, 680 uF, 20%, 450 VDC, -25/+85°C



Dimensions

D	35mm +/-1mm
L	60mm +/-2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	200

General Information

Supplier:	KEMET
Series:	ELH
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No

Specifications

Capacitance:	680 uF
Capacitance Tolerance:	20%
Voltage DC:	450 VDC, 500 VDC (Surge)
Temperature Range:	-25/+85°C
Rated Temperature:	85°C
Life:	2000 Hrs
Dissipation Factor:	20.00%
Resistance:	110 mOhms (20kHz 25C)
Ripple Current:	2900 mAmps (120Hz)
Leakage Current:	3000 uA (5min 20°C)