

PRODUCT DATASHEET

DL UNIV SN D300 V 23W ML 83040 WT

DOWNLIGHT UNIVERSAL SENSOR | Semi-recessed downlights suitable for refurbishment of existing ceiling cut-outs with integrated driver and sensor



Areas of application

- Direct replacement for luminaires with compact fluorescent lamps
- Reception areas, foyers, corridors, common areas

Product benefits

- The solution for convenient refurbishment: universal fitting to existing ceiling cut-outs
- Highly versatile due to selectable CCT and lumen steps (Multi Select)
- Simple installation thanks to integrated driver
- Energy savings thanks to high system efficacy: up to 145 lm/W
- Very homogenous light distribution
- Further variants with on/off and DALI-2 driver available

Product features

- Presence and daylight sensor control (PIR)
- Multi Color function: 3000 K and 4000 K
- Multi Lumen function: 2 lumen steps selectable
- Multi Cut-out: adjustable mounting springs for ceiling cut-outs from 65 mm up to 260 mm
- Available in two sizes: 200 mm and 300 mm diameter
- High color consistency: < 4 SDCM



- Type of protection: IP44 (room side)
- Suitable for through wiring
- Lifetime (L80/B10): up to 50,000 h (at 25 °C)


TECHNICAL DATA

Electrical data


Nominal wattage	23 W / 11 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	105 mA
Inrush current	10.4 A
Inrush current time T_{h50}	82 μ s
Max. number of luminaires per miniature circuit breaker B16	72
Max. number of luminaires per miniature circuit breaker C10	57
Max. number of luminaires per miniature circuit breaker C16	92
Power factor λ	> 0.90
Total harmonic distortion	< 50 %
Protection class	II
Operating mode	Integrated LED driver

Photometrical data


Luminous flux	3200 lm / 3100 lm / 1600 lm / 1550 lm
Luminous efficacy	140 lm/W / 135 lm/W / 145 lm/W
Color temperature	3000 K / 4000 K
Reference control setting of contained light source (Kelvin)	4000 K
Light color (designation)	Warm White / Cool White
Color rendering index Ra	> 80
Standard deviation of color matching	< 4 sdcm
Low flicker	Yes
Flickering metric (Pst LM)	<1
Stroboscope effect metric (SVM)	<0.4
Photobiological safety group acc. to EN62778	RG0
Beam angle	110 °




DL UNIV SN D300 V 23W MS 830
WT LEDV



DL UNIV SN D300 V 23W MS 840
WT LEDV



DL UNIV SN D300 V 23W MS 840
WT LEDV




DL UNIV SN D300 V 23W MS 830
WT LEDV

Adjustable attributes

Nominal wattage	Color temperature	Luminous flux	Luminous efficacy
23 W	3000 K	3100 lm	135 lm/W
23 W	4000 K	3200 lm	140 lm/W
11 W	3000 K	1550 lm	140 lm/W
11 W	4000 K	1600 lm	145 lm/W

Dimensions & Weight

Diameter	300.00 mm
Height	22.00 mm
Product weight	725.00 g



DL UNIV SN D300 V 23W ML
83040 WT

Materials & Colors

Product color	White
Housing color	White
RAL Color (most similar)	RAL 9003
Body material	Polycarbonate (PC)
Cover material	Polycarbonate (PC)
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-20...+40 °C
Temperature range at storage	-20...+80 °C
Type of connection	Screwless terminal
Type of protection	IP44/IP20
Protection class IK (shock resistance)	IK03
Dimmable	No
Mounting type	Surface/Recessed
Mounting location	Ceiling
Application environment	Indoor
Mounting diameter	65...260 mm
Mounting depth	22,0 mm
Mechanically adjustable	No
With light source	Yes
Replaceable light source	No

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	50000 h ¹⁾
Lifespan L80/B50 at 25 °C	50000 h
Lifespan L90/B10 at 25 °C	40000 h
Number of switching cycles	25000

¹⁾ t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	165mA / 82 mA
ECG - Output ripple current	< 10 %
ECG - Height	25 mm

Sensor

Type of sensor	Motion / Light
Sensor technology	Passive infrared (PIR)
Sensor detection angle	120 °
Sensor controlled switching time	5 s...3 min
Detection range of motion sensor	3...6 m
Detection threshold of daylight sensor	10...40 lx

Emergency lighting

Type of emergency operation test	None
----------------------------------	------

Certificates & Standards

Standards	CE / ENEC / UKCA / EAC / EPD
Luminaire with limited surface temperature, "D sign"	No
Ball shot safe	No
EPD	LEDV-00068-V01.01-EN
Replaceable light source (EPREL)	Not replaceable

Additional product data

Added function	MULTI SELECT
----------------	--------------

Accessories Optional

Product image	Product name	EAN
	DL UNIV SN RING D300 BN	4099854559518
	DL UNIV SN RING D300 BK	4099854559495

EQUIPMENT / ACCESSORIES

- Additional cover rings separately available in round shape and in different colors
- Safety rope for luminaire included

Safety advice

- All electrical connections must be made by a qualified person.
- Caution, risk of electric shock.
- The luminaires are not suitable for covering with thermally insulated material.

DOWNLOAD DATA

	Documents and certificates	Document name
	User instruction / safety instructions	G11249993 DOWNLIGHT UNIVERSAL
	Legal information	Informationstext 18 Abs 4 ElektroG
	Legal information	Safety Insert G11207793
	Legal information	G11252354 Light source insert
	Legal information	Legal insert DL UNIV
	Declarations of conformity	CE declaration DL UNIV
	Declarations of conformity UKCA	UKCA declaration DL UNIV
	EPD	EPD EN DOWNLIGHT UNIVERSAL


Photometric and lighting design files		Document name
	IES file (IES)	DL UNIV SN D300 V 23W MS 830 WT LEDV
	IES file (IES)	DL UNIV SN D300 V 23W MS 840 WT LEDV
	LDT file (Eulumdat)	DL UNIV SN D300 V 23W MS 830 WT LEDV
	LDT file (Eulumdat)	DL UNIV SN D300 V 23W MS 840 WT LEDV
	UGR file (UGR table)	DL UNIV SN D300 V 23W MS 830 WT LEDV
	UGR file (UGR table)	DL UNIV SN D300 V 23W MS 840 WT LEDV
	Light distribution curve type cone	DL UNIV SN D300 V 23W MS 830 WT LEDV
	Light distribution curve type cone	DL UNIV SN D300 V 23W MS 840 WT LEDV
	Light distribution curve type polar	DL UNIV SN D300 V 23W MS 830 WT LEDV
	Light distribution curve type polar	DL UNIV SN D300 V 23W MS 840 WT LEDV
CAD/BIM files		Document name
	BIM Revit 3D	Downlight-Universal
	CAD STEP 3D	DL UNIV SN D300
Tender texts		Document name
	Tender documents	DOWNLIGHT UNIVERSAL SENSOR D300 V 23W ML 83040 WT-en

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854541438	Folding box 1	315 mm x 305 mm x 60 mm	900.00 g	5.76 dm³
4099854541445	Shipping box 7	447 mm x 330 mm x 330 mm	7103.00 g	48.68 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION



References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.