

L-V 125R-FI

Pressed steel swivel castor, medium duty design, with top plate fitting, with brake system 'stop-fix', wheel, with standard solid rubber tyre, with pressed steel rim, reinforced design

EAN 4047526005726

ID 5728

Customs tariff number 87169090



Bracket: L series

- pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- strong central kingpin (from wheel Ø 150 mm)
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: V series

- tyre: standard solid rubber, hardness 80 Shore A, colour black
- rim: pressed steel, strong rim structure with tubular steel hub, bolted or pressed, zinc-plated, blue-passivated, Cr6-free

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, reduced load capacity over +60 °C

Technical data:

Wheel Ø (D)	⌀	125 mm
Wheel width	⊥	37.5 mm
Load capacity at 4 km/h	⬇	100 kg
Load capacity (static)	⬇	250 kg
Bearing type	⊙	roller bearing
Total height (H)	⊘	150 mm
Mounting type		top plate
Plate size	⊞	100 x 85 mm
Bolt hole spacing	⊞	80 x 60 mm
Bolt hole Ø	⌀	9 mm
Offset (F)	⊘	40 mm
Temperature resistance min		-25 °C
Temperature resistance max		70 °C
Tread and tyre hardness		80 Shore A
Unit weight	⚖	1.4 kg
Non-marking	×	
Non-staining	×	
Antistatic	⚡	×
ESD	×	
Electrically conductive	⚡	×
Corrosion-resistant	×	
Heat-resistant	🔥	×
Suitable for autoclaves	×	



Tread and tyre hardness

■ ■ ■ ■ ■ 80 Shore A

Rolling resistance



■ ■ ■ ■ ■ satisfactory

Wear resistance

■ ■ ■ ■ ■ sufficient

Operating noise / floor surface preservation

■ ■ ■ ■ ■ very good



Product references



Corresponding fixed castor B-V 125R



Corresponding swivel castor L-V 125R



Wheel used V 125/15R