#4118 - 7 Core Trailer Cable



Part NO: #4118

Product Code: RGW-1910

Product Description

Application:

Trailer Interconnection Cable

Multi-construction

A (6 Core) + B (1 Core)

Construction					
Conductor	A (6 Core)	B (1 Core)			
	Bare Copper	Bare Copper			
Construction	1.3 ± 0.02	1.84 ± 0.03			
Stranded Dia.(mm)	1.30	1.84			
Insulation	PVC	PVC			
Thickness(mm)	0.65	0.65			
Dia.(±0.1mm)	$2.6 \times 6C$	3.15			
Insulation Color (A) I	Brown, Blue, Black,	Yellow, Red and Green			
Insulation Color (B)	White				
Jacket	P	VC			
Thickness(mm)	0.85				

10.20

Black

Marking

According to customer


PACKAGING

Dia.(+/-0.2mm)

Jacket Color

25m reels

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω /Km)

RoHS GUIDELINE We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment		
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES		
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES		
Mercury content (Hg)	< 0.1%	EPA3052	ICP-AES		
Chromium (VI) content	< 0.1%	EPA3060(UN-VIS)	ICP-AES		
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS			
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC			

Revision History

Date:	20113-03-12	
Page:	1/1	