



Non-conductive Lockout Hasp

Overview

Non-conductive lockout hasps have exceptional electrical insulating characteristics and are made of red, glass-filled nylon material.

- Each hasp can withstand up to 46 kg, yet weighs only 25 g.
- Hasps allow multiple padlocks to secure a single lockout device
- Equipping your employees with the proper lockout tools and warning devices can save lives, reduce lost employee time, and cut insurance costs

Specifications

Key Characteristics	Article Number	325581
	Order Reference	325581
	Total Qty per Pack	1 Piece(s) / Pack
	Minimum Order Quantity	1
	Application(s) ?	Lockout tagout
	Quantity	1
	Brand	Brady®
	Country of Origin ?	China
Dimensions	Size - Width (mm)	45.11 mm
	Size - Height (mm)	154.89 mm
	Size - Depth (mm)	13.21 mm
	Hole Diameter (mm)	9.53 mm
	Max. Shackle Diameter (mm)	9.53 mm
	Min. Shackle Clearance (mm)	6.50 mm
	Dimensions	45.11 mm (W) x 154.89 mm (H) x 13.21 mm (D)
	Inside Jaw Size	14.61 mm
Material Characteristics	Brady Material Type ?	Glass-filled Nylon
	Colour	Red
	Max. Service Temp. °C	80 °C
	Min. Service Temp. °C	-20 °C
	Conductive	No
Product Features	Max number of padlocks attached ?	6
	# of Holes	6
	Risk ?	Switch and Fuse Protection
Compliance	UNSPSC ?	39121903
	RoHS Compliance Status	Please contact our CS department for more information
	REACH SVHC Status	Please contact our CS department for more information
	REACH Candidate List Date	Please contact our CS department for more information
	Product Regulations	ATEX standpoint