

## Cable marker - WMTB-AL (40X15) - 0830524

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Aluminum label, aluminum color, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: Assembly with cable binders, cable diameter: > 4.6 mm, lettering field size: 40 x 15 mm

### Product Description


Note:  
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept an aluminum alloy material quality that may cause the appearance to deviate from the homogenous surface quality that was previously expected. This has no impact on the quality of the aluminum labels themselves or the durability of the printing. The effect is purely visual.

### Your advantages

- Aluminum cable marking for assembly with cable ties
- High-quality appearance
- Suitable for large-surface marking of wires and cables, >4.6 mm in diameter



### Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 45 pc   |
| Minimum order quantity | 45 pc   |
| GTIN                   | <br>4 046356 718660 |
| GTIN                   | 4046356718660   |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 59 mm |
| Width (a)  | 15 mm |

#### Ambient conditions

|                                |                |
|--------------------------------|----------------|
| Recommended storage conditions | 5 °C ... 25 °C |
|--------------------------------|----------------|

#### General

|       |                |
|-------|----------------|
| Color | aluminum color |
| Type  | Roll           |

# Cable marker - WMTB-AL (40X15) - 0830524

## Technical data

### General

|  |  |
|--|--|
| Components   | free from silicone, halogen, and cadmium       |
| Material   | Aluminum                                       |
| Wipe resistance  | DIN EN 61010-1 (VDE 0411-1)                    |
| Marking mounting type  | Assembly with cable binders                    |
| Min. cross section   | 16 mm <sup>2</sup>                             |
| Testing substances harmful to the wetting properties of lacquers (LABS conformity) | VW PV 3.10.7:2005-02                           |
| Result   | Test passed                                    |
| UV resistance  | Following ISO 4892-2:2013-03                   |
| Result   | Test passed                                    |
| Test duration  | 96 h   |
| Test for wipe resistance of inscriptions   | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|  | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Testing in a condensation changing climate in the presence of sulfur dioxide       | following DIN 50018:2013-05                    |
| Result   | Test passed                                    |
| Climate level  | AHT 1,0 S                                      |
| Cycles   | 2  |
| Salt spray test  | DIN EN 60068-2-11:2000-02                      |
| Result   | Test passed                                    |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400401 |
| eCl@ss 11.0   | 27281102 |
| eCl@ss 4.0    | 27061700 |
| eCl@ss 4.1    | 27061700 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27400400 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 9.0    | 27400401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 6.01 | 30211811 |
|-------------|----------|

## Cable marker - WMTB-AL (40X15) - 0830524

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

### Accessories

#### Accessories

#### Magazine

Magazine - BLUEMARK MAG WM-M (40X15) - 0802744



Magazine, width: 76 mm, color: white

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>