


Features

- Rigid steel construction provides excellent stability and vibration resistance for consistent turning performance..
- Designed for negative inserts with a secure MTP P clamping system for reliable insert retention.
- Right-hand holder with 95° cutting edge angle, ideal for precise external turning and facing operations.

RS PRO Turning Holders for use with 06 WNMG Inserts



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro PWNLR Turning Holder is a right-hand tool holder designed for use with negative WNMG 06 inserts, offering reliable performance in external turning and facing operations. Manufactured from high quality steel, it provides excellent rigidity and stability, helping to achieve consistent results. Featuring 95° cutting edge angle, with a secure MTP P clamping system.

General Specifications

Brand	RS PRO
Sub Type	Lathe Tool Holder
Product Type	Lathe Part
Approach Angle	95°
For Use With	WNMG 06
Overall Length	125mm – 150mm
Overall Height	25mm – 32mm
Shank Height	20mm – 25mm
Shank Width	20mm – 25mm
Insert Inscribed Circle	9.53mm
Hand	Right

Mechanical Specifications

Shank Height	H – See table below and detailed image below
Head of Cutting Head Section	HF – See table below and detailed image below
Shank Width	B – See table below and detailed image below
Overall Holder Length	LF – See table below and detailed image below
Width of Cutting Head Section	WF – See table below and detailed image below

Approvals

Declarations	N/A
Hazardous Area Certification	N/A
Standards Met	N/A

Stock No.	Brand	H	HF	B	LF	WF
XXX-XXXX 900445	RS PRO	20	20	20	125	25
XXX-XXXX 900446	RS PRO	25	25	25	150	32

Similar Products

Stock No.	Brand	LE	IC	S	RE	Feed per rev fn	Depth of cut ap
XXX-XXXX 900318	RS PRO	5.7	9.53	4.76	0.4	0.5 - 0.20	0.5 - 2.0

Stock No.	Brand	LE	IC	S	RE	Feed per rev fn	Depth of cut ap
XXX-XXXX 900312	RS PRO	5.7	9.53	4.76	0.8	0.20 - 0.40	1.0 - 2.5

Stock No.	Brand	LE	IC	S	RE	Feed per rev fn	Depth of cut ap
XXX-XXXX 900317	RS PRO	5.7	9.53	4.76	0.8	0.20 - 0.40	1.0 - 3.0

Stock No.	Brand	LE	IC	S	RE	Feed per rev fn	Depth of cut ap
XXX-XXXX 900319	RS PRO	5.7	9.53	4.76	1.2	0.30 - 0.50	1.5 - 4.0

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

