

# Product datasheet

Specifications



## processor module M340 - max 1024 discrete + 256 analog I/O - Modbus - Ethernet

Local distributor code:  
393393327

BMXP342020H

EAN Code: 3595864009766

## Main

Range of product	Modicon M340 automation platform
Product or component type	Processor module
Product specific application	For severe environments
Concept	Transparent Ready Modbus
Number of racks	4
Local I/O processor capacity (discrete)	1024 I/O
Analogue I/O processor capacity	256 I/O
Number of application specific channel	36
Monitoring	Diagnostic counters Modbus Event counters Modbus

## Complementary

Control channels	Programmable loops
Integrated connection type	Non isolated serial link RJ45 character mode, transmission mode: asynchronous in baseband, RS232C, transmission mode: 2 twisted shielded pairs at 0.3...19.2 kbit/s full duplex Non isolated serial link RJ45 character mode, transmission mode: asynchronous in baseband, RS485, transmission mode: 1 twisted shielded pair at 0.3...19.2 kbit/s half duplex Non isolated serial link RJ45, master/slave Modbus, RTU/ASCII, transmission mode: asynchronous in baseband, RS232C, transmission mode: 1 twisted shielded pair at 0.3...19.2 kbit/s half duplex Non isolated serial link RJ45, master/slave Modbus, RTU/ASCII, transmission mode: asynchronous in baseband, RS485, transmission mode: 1 twisted shielded pair at 0.3...19.2 kbit/s half duplex USB port at 12 Mbit/s Ethernet TCP/IP RJ45, transmission mode: 1 twisted pair at 10/100 Mbit/s
Communication module processor capacity	2 Ethernet communication module 4 AS-Interface module
embedded communication service	Bandwidth management, Ethernet TCP/IP Data Editor, Ethernet TCP/IP Modbus TCP messaging, Ethernet TCP/IP Rack Viewer, Ethernet TCP/IP SNMP network administrator, Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX
Number of devices per segment	0...32 (character mode) 0...32 (Modbus)
Number of devices	2 point-to-point character mode 2 point-to-point Modbus

<b>Bus length</b>	0...10 m serial link non isolated character mode segment 0...10 m serial link non isolated Modbus segment 0...1000 m serial link isolated character mode segment 0...1000 m serial link isolated Modbus segment 0...15 m character mode point-to-point 0...15 m Modbus point-to-point
<b>Maximum tap links length</b>	<15 m serial link non isolated character mode segment <15 m serial link non isolated Modbus segment <40 m serial link isolated character mode segment <40 m serial link isolated Modbus segment
<b>Number of addresses</b>	0...248 for character mode 0...248 for Modbus
<b>Requests</b>	1 K data bytes per request character mode 252 data bytes per RTU request Modbus 504 data bytes per ASCII request Modbus
<b>Control parameter</b>	One CRC on each frame (RTU) Modbus One LRC on each frame (ASCII) character mode One LRC on each frame (ASCII) Modbus
<b>Memory description</b>	Supplied memory card (BMXRMS008MP) backup of programs, constants, symbols and data Internal RAM 4096 kB Internal RAM 256 kB data Internal RAM 3584 kB program constants and symbols Supplied memory card (BMXRMS008MP) activation of standard web server, class B10
<b>Maximum size of object areas</b>	32634 %Mi located internal bits 32464 %MWi internal words 32760 %KWi constant words
<b>Default size of object areas</b>	1024 %MWi internal words located internal data 256 %KWi constant words located internal data 512 %Mi located internal bits
<b>Application structure</b>	64 event tasks 1 periodic fast task No auxiliary task 1 cyclic/periodic master task
<b>Execution time per instruction</b>	0.12 $\mu$ s Boolean 0.17 $\mu$ s double-length words 0.25 $\mu$ s single-length words 1.16 $\mu$ s floating points
<b>Number of instructions per ms</b>	6.4 Kinst/ms 65 % Boolean + 35 % fixed arithmetic 8.1 Kinst/ms 100 % Boolean
<b>System overhead</b>	0.13 ms for fast task 0.7 ms for master task
<b>Current consumption</b>	95 mA at 24 V DC
<b>Supply</b>	Internal power supply via rack
<b>Marking</b>	CE UL CSA RCM EAC UKCA China RoHS WEEE IEC ATEX
<b>Status LED</b>	1 LED (green) activity on Ethernet network (ETH ACT) 1 LED (green) processor running (RUN) 1 LED (green) status of Ethernet network (ETH STS) 1 LED (green) data rate (ETH 100) 1 LED (red) I/O module fault (I/O) 1 LED (red) memory card fault (CARD ERR) 1 LED (red) processor or system fault (ERR) 1 LED (yellow) activity on Modbus (SER COM)
<b>Net weight</b>	0.205 kg

## Environment

Ambient air temperature for operation	-25...70 °C
Relative humidity	5...95 % without condensation
IP degree of protection	IP20
Protective treatment	Conformal coating
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2012/19/EU - WEEE directive 2014/34/EU - ATEX directive
Product certifications	CE UL CSA RCM EAC UKCA Merchant Navy ATEX zone 2/22 IEC-Ex zone 2/22 UKEX zone 2/22 CCSAus HazLoc Class I Division 2 Group A CCSAus HazLoc Class I Division 2 Group B CCSAus HazLoc Class I Division 2 Group C CCSAus HazLoc Class I Division 2 Group D
Standards	IEC 61131-2 IEC 61010-2-201 UL 61010-2-201 CSA C22.2 No 61010-2-201 IACS E10 EN/IEC 61000-6-5, interface type 1 and type 2 EN/IEC 61850-3, location G IEC 60079-0
Environmental characteristic	Gas resistant class Gx conforming to ISA S71.04 Gas resistant class 3C4 conforming to IEC 60721-3-3 Dust resistant class 3S4 conforming to IEC 60721-3-3 Sand resistant class 3S4 conforming to IEC 60721-3-3 Salt resistant Kb/2 conforming to IEC 60068-2-52 Mold growth resistant class 3B2 conforming to IEC 60721-3-3 Fungal spore resistant class 3B2 conforming to IEC 60721-3-3

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.600 cm
Package 1 Width	11.700 cm
Package 1 Length	12.000 cm
Package 1 Weight	255.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.033 kg

## Logistical informations

Country of origin	FR
-------------------	----

# Contractual warranty

---

Warranty (in months)

18



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	119 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	17 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	102 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.4 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Reference contains Substances of Very High Concern above the threshold</a>

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Recyclability potential, in %	32
End of life manual availability	<a href="#">End of Life Information</a>
Take-back	Nej

Dimensions Drawings

Modules Mounted on Racks

---

Dimensions



- (1) With removable terminal block (cage, screw or spring).
- (2) With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81

Image of product / Alternate images

Alternative

---

