

## Mini1 Smartphone Module



The Smartphone Module is designed to inspect electrical equipment, troubleshooting HVAC problems. Equipped with functional thermal App for smartphone, the Smartphone Module enables you to get the thermal imaging on your phone.

### Key Features

- Thermal resolution: 160 × 120 (19 200 pixels)
- NETD: < 40 mK (@ 25 °C, F#=1.0)
- Accuracy:  $\pm 2$  °C (-20 °C to 100 °C) ;  $\pm 2$  % (100 °C to 350 °C)
- USB Type-C Interface (Android)
- 26 g Weight

## Specification

<b>Thermal Module</b>	
Image Sensor	Vanadium Oxide Uncooled Focal Plane Arrays
IR Resolution	160 × 120 (19 200 pixels)
Pixel Pitch	17 μm
Spectrum Range	8 - 14 μm
NETD	< 40 mK (@ 25 °C, F#=1.0)
Focal Length	3.2 mm
FOV (Field of View)	50° × 38° (H × V)
Minimum Focus Distance	20 cm
Focus	Fixed
Image Frequency	25 Hz
Aperture	F1.1
<b>Thermography Function</b>	
Accuracy	±2 °C (-20 °C to 100 °C) ; ±2 % (100 °C to 350 °C)
Object Temperature Range	-20 °C to 350 °C
Shutter	Automatic/Manual
<b>General</b>	
Power	Powered by Smartphone
Phone	Android (USB Type-C Interface)
Working Temperature Range	15 °C to 35 °C
Storage Temperature Range	-20 °C to 60 °C
Protection Level	IP40
Mechanical shock	Drop from 1 m
Weight	26 g
Dimension	54.1 mm × 15 mm × 27.5 mm
Power Consumption	300mW
<b>APP</b>	
Measurement Presets	Hot Spot, Cold Spot, Center Spot, 1 User Preset Point, 1 User Preset Box, Off
Color Palettes	Black hot, White hot, Red hot, Rainbow, Ironbow, Fusion, Rain
Video Format	MP4
Image Format	JPEG

## Available Model

HM-TJ11-3AMF-Mini1

## Packing List





Storage bag (x1)



QSG (x1)

## Dimension



Unit:mm[Inch]